

## Weiche Aufsatzbacken

|  | Bezeichnung | Ident.-Nr. | N<br>[mm] | S<br>[mm] | B<br>[mm] | H1<br>[mm] | H2<br>[mm] | L<br>[mm] | L1<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|--|-------------|------------|-----------|-----------|-----------|------------|------------|-----------|------------|-----------|-----------|-----------|----------------|
|  | WA-RN 200   | 0151101    | 7.96      | 12.67     | 30        | 50         | 47         | 87        | 38.7       | 44.5      | M8        | Stahl     | 0.84           |

