

Chuck			Dimensions			Specs.						Price
Brand	Typ	Chuck size	Chuck outside diameter	Chuck-height	Weight	max. RPM	Max. actuating force	Max. clamping force	Pistion stroke	Stroke/jaw	Pendular compensation	Listprice
			mm	mm	kg	1/min	kN	kN	mm	mm	mm +/-	€ /pc.
Schunk	ROTA NCR-A	190	✓ 190	82	✓ 14	4.000	22	36	13,50	6	1	7.585,00 €
SMW	SJL-C	225	225	101	26	4.200	30	45	11,50	6	1	10.091,00 €
Schunk	ROTA NCR-A-F	250	250	107	36	3.000	38	✓ 64	18,50	✓ 8	✓ 2	12.044,00 €
SMW	SJL-M	225	225	103,5	26	4.200	30	45	11,50	6	1	10.091,00 €
Schunk	ROTA NCR-A-F	315	315	✓ 107	55	2.500	40	✓ 80	20,00	8	✓ 2	16.042,00 €
SMW	SJL-M	290	290	131	51	3.600	42	65	15,00	8	1	12.944,00 €
Schunk	ROTA NCR-A-F	400	400	✓ 145	✓ 118	1.400	54	✓ 100	30,00	✓ 12	2,5	23.760,00 €
SMW	SJL-M	400	400	181	136	2.600	58	90	20,80	11	2,5	22.487,00 €
Schunk	ROTA NCR-A-F	400	400	✓ 145	✓ 118	1.400	54	100	30,00	✓ 12	2,5	23.760,00 €
SMW	IEP-D	400	419	154	145	1.600	90	130	20,00	10	2,5	
Schunk	ROTA NCR-A-F	500	500	✓ 145	✓ 175	✓ 1.200	65	125	30,00	12	2,5	32.277,00 €
SMW	IEP-D	500	510	184	260	1.100	120	180	30,00	15	4	26.886,00 €
Schunk	ROTA NCR-A-F	630	630	199	✓ 387	✓ 1.000	80	160	40,00	✓ 16	3,5	46.535,00 €
SMW	IEP-D	630	630	184	410	800	120	180	30,00	15	4	38.767,00 €
Schunk	ROTA NCR-A	800	800	199	✓ 495	✓ 700	80	160	40,00	16	3,5	58.554,00 €
SMW	IEP-D	800	800	184	670	650	120	180	30,00	15	4	55.409,00 €
Schunk	ROTA NCR-A	1000	1000	261	1300	✓ 600	150	300	60,00	✓ 25	✓ 6	83.497,00 €
SMW	IEP-D	1000	1005	254	1100	450	200	300	40,00	20	5	79.015,00 €

Notice:

The 6 jaw chuck SJL from SMW are all with centrifugal force compensation

so this was compard with our ROTA NCR-A-F.

For smaller sizes, SMW pnly has size 225,

SCHUNK has size 190 + 250.



= Customer's benefit when choosing SCHUNK

A. Nusser

2021-02-15