



Hand in hand for tomorrow



Product data sheet

Feed-through modules COS HB6

Robust. Reliable. Flexible.

Optional modules COS

Optional modules for feeding through different media such as electrical signals, pneumatics, fluids and vacuum.

Field of application

For fast media transfer with short change-over times between change master and change adapter in order to supply the end effector with the required media.

Advantages – Your benefits

Fits perfectly for easy combination with SCHUNK tool changers

Wide range of different variants for feeding through of various media

Module variety the appropriate module for the required media transfer for every size of SCHUNK tool changers

Connector variants with radial, axial, and side cable outlet for a low interfering contour in restricted spaces

Combination of several optional modules for maximum flexibility of the tool changer

Minimum wear for a high number of change cycles and a long service life

Customer-specific designs available on request the suitable solution for any application

Cable connector, cable extensions and protection covers available on request for a comprehensive complete solution from one source



Application example



① Automatic tool changers CPS

③ Modular storage rack CTS

⑤ 2-finger parallel gripper JGP-P

② Optional modules COS

④ Universal gripper EGU

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Tool changer




Manual change system



Pallet change system

① For more information on these products can be found on the following product pages or at [schunk.com](https://www.schunk.com).

Overview of optional modules and mounting pattern



Special designs with modified seals or lubrication are available on request

COS HB6


Feed-through modules



Technical data

Description		COS HB6-K	COS HB6-A
ID		1586289	1586287
Suitable on		Change head	Tool
Screw connection diagram		L	L
Transmission type		Hydraulics	Hydraulics
Weight	[kg]	1.47	1.3
Min./max. ambient temperature	[°C]	5/60	5/60
Outlet connection		axial	axial
No. of fluid feed-throughs		2x G3/8"	2x G3/8"
Type of medium		Hydraulic, water	Hydraulic, water
Max. volumetric flow per fluid feed-through		1.460 l/min (G3/8")	1.460 l/min (G3/8")
Max. operating pressure	[bar]	496	496
Special properties		Hydraulic module for the transmission of hydraulic fluid up to 496 bar operating pressure	Hydraulic module for the transmission of hydraulic fluid up to 496 bar operating pressure


Combination COS HB6-K and COS HB6-A



12 Master side

13 Adapter side

Cover COS HC2-A



90 Automatic tool changers CPS

92 Cover COS HC2-A

91 Optional module COS master

Description	ID	Suitable for
Cover		
COS HC2-A	1586300	Hydraulic modules COS HB2-K and COS HB6-K



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

info@de.schunk.com

schunk.com

Folgen Sie uns | *Follow us*

