



Hand in hand for tomorrow



Product data sheet

Feed-through modules COS FH12

Robust. Reliable. Flexible.

Optional modules COS

Optional modules for feeding through different media such as electrical signals, pneumatics, fluids and vacuum.

Field of application

For fast media transfer with short change-over times between change master and change adapter in order to supply the end effector with the required media.

Advantages – Your benefits

Fits perfectly for easy combination with SCHUNK tool changers

Wide range of different variants for feeding through of various media

Module variety the appropriate module for the required media transfer for every size of SCHUNK tool changers

Connector variants with radial, axial, and side cable outlet for a low interfering contour in restricted spaces

Combination of several optional modules for maximum flexibility of the tool changer

Minimum wear for a high number of change cycles and a long service life

Customer-specific designs available on request the suitable solution for any application

Cable connector, cable extensions and protection covers available on request for a comprehensive complete solution from one source



Application example



① Automatic tool changers CPS

③ Modular storage rack CTS

⑤ 2-finger parallel gripper JGP-P

② Optional modules COS

④ Universal gripper EGU

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Tool changer




Manual change system



Pallet change system

① For more information on these products can be found on the following product pages or at [schunk.com](https://www.schunk.com).

Overview of optional modules and mounting pattern




Special designs with modified seals or lubrication are available on request



Technical data

Description		COS FH12-K	COS FH12-A
ID		1586540	1586509
Suitable on		Change head	Tool
Screw connection diagram		L	L
Transmission type		liquids	liquids
Weight	[kg]	2.9	2.27
Min./max. ambient temperature	[°C]	5/60	5/60
Outlet connection		radial	radial
No. of fluid feed-throughs		4x G1/2"	4x G1/2"
Type of medium		Air, water	Air, water
Max. volumetric flow per fluid feed-through		1.460 l/min (G1/2")	1.460 l/min (G1/2")
Max. operating pressure	[bar]	6.9	6.9
Special properties		self-sealing ports, stainless steel housing	self-sealing ports, stainless steel housing

Combination COS FH12-K and COS FH12-A



⑫ Master side

⑬ Adapter side



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

info@de.schunk.com

schunk.com

Folgen Sie uns | *Follow us*

