






# Spannkraftprüfer



## Technische Daten

| Bezeichnung         | ID                       | Für Schnittstelle | D1<br>[mm] | D2<br>[mm] | L1<br>[mm] | L2<br>[mm] | Gewicht<br>[kg] |
|---------------------|--------------------------|-------------------|------------|------------|------------|------------|-----------------|
| SKP HSK 20          | <a href="#">1545627</a>  | HSK 20            | 20         | 29         | 98         | 196        | 0.8             |
| SKP HSK 25          | <a href="#">0205960</a>  | HSK 25            | 29         | 29         | 98         | 200        | 0.8             |
| SKP HSK 32          | <a href="#">0205961</a>  | HSK 32            | 32         | 36.5       | 102        | 205        | 1               |
| SKP HSK 40          | <a href="#">0205962</a>  | HSK 40            | 40         | 45         | 101        | 209        | 1.31            |
| SKP HSK 50          | <a href="#">0205963</a>  | HSK 50            | 50         | 54.5       | 104        | 216        | 1.74            |
| SKP HSK 63          | <a href="#">0205964</a>  | HSK 63            | 63         | 54.5       | 130        | 248        | 2.6             |
| SKP HSK 80          | <a href="#">0205965</a>  | HSK 80            | 80         | 54.5       | 135        | 263        | 3.48            |
| SKP HSK 100         | <a href="#">0205966</a>  | HSK 100           | 100        | 68         | 137        | 273        | 5.54            |
| SKP SK 30/CAT 30    | <a href="#">1336529</a>  | SK 30/CAT 30      | 31.75      | 18         | 112.2      | 223        | 1.05            |
| SKP SK 40/CAT 40    | <a href="#">20041741</a> | SK 40/CAT 40      | 44.45      | 24         | 141.6      | 255        | 1.88            |
| SKP SK 50/CAT 50    | <a href="#">20043854</a> | SK 50/CAT 50      | 69.85      | 39         | 155.25     | 292        | 3.46            |
| SKP BT 30/BT-DC 30  | <a href="#">20057197</a> | BT 30/BT-DC 30    | 31.75      | 18         | 112.2      | 223        | 1.05            |
| SKP BT 40/BT-DC 40  | <a href="#">1319084</a>  | BT 40/BT-DC 40    | 44.45      | 24         | 141.6      | 255        | 1.88            |
| SKP SCHUNK CAPTO C5 | <a href="#">20050084</a> | SCHUNK CAPTO C5   | 50         | 54.5       | 109        | 226        | 2.06            |
| SKP SCHUNK CAPTO C6 | <a href="#">20057025</a> | SCHUNK CAPTO C6   | 63         | 67.5       | 119        | 244        | 3.16            |





**SCHUNK SE & Co. KG**

**Spanntechnik**

**Greiftechnik**

**Automatisierungstechnik**

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

[CMS@de.schunk.com](mailto:CMS@de.schunk.com)

[schunk.com](http://schunk.com)