




Datenträger



Technische Daten

Bezeichnung	ID	Durchmesser D	Länge L	Speicherkapa- zität	IP Schutzklasse	Min./max. Umgebungs- temperatur [°C]	Min./max. Lagertempe- ratur [°C]	Gehäusematerial
		[mm]	[mm]					
BIS-C-122-04-L	9905355	10	4.5	511 Byte	68	0 - 70	-30 - 85	Epoxidharz-Glasfaser
BIS-C-122-11-L	23002833	10	4.5	2047 Byte	68	0 - 70	-30 - 85	Epoxidharz-Glasfaser
BIS-M-122-02/A	23002987	10	4.5	2000 Byte	67	-25 - 70	-25 - 85	PA 12, PU Verguss
BIS-C-122-05-L	1497154	10	4.5	1023 Byte	68	0 - 70	-30 - 85	Epoxidharz-Glasfaser



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com