






Skúšačka upínacej sily

Skúšačka upínacej sily
Všeobecné príslušenstvo



Technické údaje

Opis	ID	Pre rozhranie	D1 [mm]	D2 [mm]	L1 [mm]	L2 [mm]	Hmotnosť [kg]
SKP HSK 20	1545627	HSK 20	20	29	98	196	0.8
SKP HSK 25	0205960	HSK 25	29	29	98	200	0.8
SKP HSK 32	0205961	HSK 32	32	36.5	102	205	1
SKP HSK 40	0205962	HSK 40	40	45	101	209	1.31
SKP HSK 50	0205963	HSK 50	50	54.5	104	216	1.74
SKP HSK 63	0205964	HSK 63	63	54.5	130	248	2.6
SKP HSK 80	0205965	HSK 80	80	54.5	135	263	3.48
SKP HSK 100	0205966	HSK 100	100	68	137	273	5.54
SKP SK 30/CAT 30	1336529	SK 30/CAT 30	31.75	18	112.2	223	1.05
SKP SK 40/CAT 40	20041741	SK 40/CAT 40	44.45	24	141.6	255	1.88
SKP SK 50/CAT 50	20043854	SK 50/CAT 50	69.85	39	155.25	292	3.46
SKP BT 30/BT-DC 30	20057197	BT 30/BT-DC 30	31.75	18	112.2	223	1.05
SKP BT 40/BT-DC 40	1319084	BT 40/BT-DC 40	44.45	24	141.6	255	1.88
SKP SCHUNK CAPTO C5	20050084	SCHUNK CAPTO C5	50	54.5	109	226	2.06
SKP SCHUNK CAPTO C6	20057025	SCHUNK CAPTO C6	63	67.5	119	244	3.16



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com