


Cleaning accessories

Cylindrical brush



Technical data

Description	Description	ID	For clamping diameter	Weight [kg]
Zylinderbürste 6	Cleaning brush 6	9102002	6 mm	0.03
Zylinderbürste 8	Cleaning brush 8	9102003	8 mm	0.03
Zylinderbürste 10	Cleaning brush 10	9102004	10 mm	0.03
Zylinderbürste 12	Cleaning brush 12	9102005	12 mm	0.03
Zylinderbürste 16	Cleaning brush 16	9102017	16 mm	0.04
Zylinderbürste 20	Cleaning brush 20	9102007	20 mm	0.04
Zylinderbürste 25	Cleaning brush 25	9102009	25 mm	0.04
Zylinderbürste 32	Cleaning brush 32	9102016	32 mm	0.04




Technical data

Description	Description	ID	For clamping diameter	Weight [kg]
TK-Cleaner TKC 6	TK-Cleaner TKC 6	0280010	6 mm	0.045
TK-Cleaner TKC 8	TK-Cleaner TKC 8	0280011	8 mm	0.045
TK-Cleaner TKC 10	TK-Cleaner TKC 10	0280012	10 mm	0.045
TK-Cleaner TKC 12	TK-Cleaner TKC 12	0280013	12 mm	0.044
TK-Cleaner TKC 14	TK-Cleaner TKC 14	0280014	14 mm	0.044




Technical data

Description	Description	ID	For clamping diameter	Weight [kg]
TK-Cleaner TKC 16	TK-Cleaner TKC 16	0280015	16 mm	0.042
TK-Cleaner TKC 18	TK-Cleaner TKC 18	0280016	18 mm	0.044
TK-Cleaner TKC 20	TK-Cleaner TKC 20	0280017	20 mm	0.052
TK-Cleaner TKC 25	TK-Cleaner TKC 25	0280018	25 mm	0.052
TK-Cleaner TKC 32	TK-Cleaner TKC 32	0280019	32 mm	0.089
TK-Cleaner TKC 40	TK-Cleaner TKC 40	27000350	40 mm	0.09
TK-Cleaner TKC 42	TK-Cleaner TKC 42	27000351	42 mm	0.095




Technical data

Description	ID	For interface	Weight [kg]
Cone wiper HSK 32	23005129	HSK 32	0.02
Cone wiper HSK 40	23005130	HSK 40	0.04
Cone wiper HSK 50	23005131	HSK 50	0.045
Cone wiper HSK 63	23002483	HSK 63	0.05
Cone wiper HSK 80	23005132	HSK 80	0.55
Cone wiper HSK 100	23005133	HSK 100	0.6



Technical data

Description	ID	Weight	Min./max. ambient temperature	Max. permissible RPM	Max. operating pressure	Dimensions Ø D x Z
		[kg]	[°C]	[min ⁻¹]	[bar]	[mm]
RGG 20	0308590	0.1	-10 - 90	100	80	37 - 78



Technical data

Description	ID	For interface	Weight [kg]
Tapered cleaner SK/BT/CAT 30	0212211	SK 30/BT 30/CAT 30	0.03
Tapered cleaner SK/BT/CAT 40	27001419	SK 40/BT 40/CAT 40	0.063
Tapered cleaner SK/BT/CAT 50	27001086	SK 50/BT 50/CAT 50	0.08



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com