



TRIBOS SVP




Technical data

Description	ID	Weight [kg]
TRIBOS SVP-2	0211760	39



Technical data

Description	ID	Weight [kg]	Mains voltage
TRIBOS SVP-2D	0211762	41.5	90 - 264 V



Technical data

Description	ID	Weight [kg]	Mains voltage
TRIBOS SVP-5	1612996	145	400 V




Technical data

Description	ID	Weight [kg]
TRIBOS SVP-2D/2D-H Scanner	0201756	0.6



Technical data

Description	ID	Weight [kg]
TRIBOS SVP-2D/2D-H Fixscanner I	0201754	0.4
TRIBOS SVP-2D/2D-H Fixscanner II	0201755	0.025



Technical data

Description	ID	Width B [mm]	Height H [mm]	Depth T [mm]	Weight [kg]
TRIBOS SVP-M	0211768	260	190	390	8.9




Technical data

Description	ID	Weight [kg]
TRIBOS SVP-M Cover	9937963	0.005




Technical data

Description	ID	Weight [kg]
TRIBOS SVP-2/SVP-2D Cover	9935548	0.2




Technical data

Description	ID	Weight [kg]
TRIBOS-Mini SVP Ø6.65	1357071	0.7
TRIBOS-Mini SVP Ø9	0211763	0.7



Technical data

Description	ID	Weight [kg]
TRIBOS-RM SVP Ø14	1346220	1.95
TRIBOS-RM SVP Ø18	1357074	1.95
TRIBOS-RM SVP Ø20	0211764	5.6



Technical data

Description	Description	ID	Weight [kg]
TRIBOS-RM/-Mini SVP Montagevorrichtung	TRIBOS-RM/-Mini SVP assembly device	9954724	0.829



Technical data

Description	ID	Weight [kg]
TRIBOS LMG-M	0201961	1.24



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com