


清洁配件




技术参数

描述	描述	ID	用于夹持直径	重量 [kg]
Zylinderbürste 6	清洁刷 6	9102002	6 mm	0.03
Zylinderbürste 8	清洁刷 8	9102003	8 mm	0.03
Zylinderbürste 10	清洁刷 10	9102004	10 mm	0.03
Zylinderbürste 12	清洁刷 12	9102005	12 mm	0.03
Zylinderbürste 16	清洁刷 16	9102017	16 mm	0.04
Zylinderbürste 20	清洁刷 20	9102007	20 mm	0.04
Zylinderbürste 25	清洁刷 25	9102009	25 mm	0.04
Zylinderbürste 32	清洁刷 32	9102016	32 mm	0.04




技术参数

描述	描述	ID	用于夹持直径	重量 [kg]
TK-Cleaner TKC 6	TK-Cleaner TKC 6	0280010	6 mm	0.045
TK-Cleaner TKC 8	TK-Cleaner TKC 8	0280011	8 mm	0.045
TK-Cleaner TKC 10	TK-Cleaner TKC 10	0280012	10 mm	0.045
TK-Cleaner TKC 12	TK-Cleaner TKC 12	0280013	12 mm	0.044
TK-Cleaner TKC 14	TK-Cleaner TKC 14	0280014	14 mm	0.044




技术参数

描述	描述	ID	用于夹持直径	重量 [kg]
TK-Cleaner TKC 16	TK-Cleaner TKC 16	0280015	16 mm	0.042
TK-Cleaner TKC 18	TK-Cleaner TKC 18	0280016	18 mm	0.044
TK-Cleaner TKC 20	TK-Cleaner TKC 20	0280017	20 mm	0.052
TK-Cleaner TKC 25	TK-Cleaner TKC 25	0280018	25 mm	0.052
TK-Cleaner TKC 32	TK-Cleaner TKC 32	0280019	32 mm	0.089
TK-Cleaner TKC 40	TK-Cleaner TKC 40	27000350	40 mm	0.09
TK-Cleaner TKC 42	TK-Cleaner TKC 42	27000351	42 mm	0.095




技术参数

描述	ID	面向接口	重量 [kg]
锥形擦拭器 HSK 32	23005129	HSK 32	0.02
锥形擦拭器 HSK 40	23005130	HSK 40	0.04
锥形擦拭器 HSK 50	23005131	HSK 50	0.045
锥形擦拭器 HSK 63	23002483	HSK 63	0.05
锥形擦拭器 HSK 80	23005132	HSK 80	0.55
锥形擦拭器 HSK 100	23005133	HSK 100	0.6



技术参数

描述	ID	重量 [kg]	最低/最高环境温度 [°C]	最大允许转速 (RPM) [min ⁻¹]	最大工作压力 [bar]	尺寸 □ D x Z [mm]
RGG 20	0308590	0.1	-10 - 90	100	80	37 - 78



技术参数

描述	ID	面向接口	重量 [kg]
锥形清洁剂 SK/BT/CAT 30	0212211	SK 30/BT 30/CAT 30	0.03
锥形清洁剂 SK/BT/CAT 40	27001419	SK 40/BT 40/CAT 40	0.063
锥形清洁剂 SK/BT/CAT 50	27001086	SK 50/BT 50/CAT 50	0.08



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 – 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com