


청소용품




기술 데이터

설명	설명	ID	클램핑 지름용	중량 [kg]
Zylinderbürste 6	청소 브러시 6	9102002	6 mm	0.03
Zylinderbürste 8	청소 브러시 8	9102003	8 mm	0.03
Zylinderbürste 10	청소 브러시 10	9102004	10 mm	0.03
Zylinderbürste 12	청소 브러시 12	9102005	12 mm	0.03
Zylinderbürste 16	청소 브러시 16	9102017	16 mm	0.04
Zylinderbürste 20	청소 브러시 20	9102007	20 mm	0.04
Zylinderbürste 25	청소 브러시 25	9102009	25 mm	0.04
Zylinderbürste 32	청소 브러시 32	9102016	32 mm	0.04




기술 데이터

설명	설명	ID	클램핑 지름용	중량 [kg]
TK-Cleaner TKC 6	TK-Cleaner TKC 6	0280010	6 mm	0.045
TK-Cleaner TKC 8	TK-Cleaner TKC 8	0280011	8 mm	0.045
TK-Cleaner TKC 10	TK-Cleaner TKC 10	0280012	10 mm	0.045
TK-Cleaner TKC 12	TK-Cleaner TKC 12	0280013	12 mm	0.044
TK-Cleaner TKC 14	TK-Cleaner TKC 14	0280014	14 mm	0.044




기술 데이터

설명	설명	ID	클램핑 지름용	중량 [kg]
TK-Cleaner TKC 16	TK-Cleaner TKC 16	0280015	16 mm	0.042
TK-Cleaner TKC 18	TK-Cleaner TKC 18	0280016	18 mm	0.044
TK-Cleaner TKC 20	TK-Cleaner TKC 20	0280017	20 mm	0.052
TK-Cleaner TKC 25	TK-Cleaner TKC 25	0280018	25 mm	0.052
TK-Cleaner TKC 32	TK-Cleaner TKC 32	0280019	32 mm	0.089
TK-Cleaner TKC 40	TK-Cleaner TKC 40	27000350	40 mm	0.09
TK-Cleaner TKC 42	TK-Cleaner TKC 42	27000351	42 mm	0.095




기술 데이터

설명	ID	인터페이스용	중량 [kg]
원뿔형 와이퍼 HSK 32	23005129	HSK 32	0.02
원뿔형 와이퍼 HSK 40	23005130	HSK 40	0.04
원뿔형 와이퍼 HSK 50	23005131	HSK 50	0.045
원뿔형 와이퍼 HSK 63	23002483	HSK 63	0.05
원뿔형 와이퍼 HSK 80	23005132	HSK 80	0.55
원뿔형 와이퍼 HSK 100	23005133	HSK 100	0.6



기술 데이터

설명	ID	중량 [kg]	최저/최고 주위 온도 [°C]	최대 허용 가능 RPM [min ⁻¹]	최대 작동 압력 [bar]	치수 Ø D x Z [mm]
RGG 20	0308590	0.1	-10 - 90	100	80	37 - 78



기술 데이터

설명	ID	인터페이스용	중량 [kg]
테이퍼 클리너 SK/BT/CAT 30	0212211	SK 30/BT 30/CAT 30	0.03
테이퍼 클리너 SK/BT/CAT 40	27001419	SK 40/BT 40/CAT 40	0.063
테이퍼 클리너 SK/BT/CAT 50	27001086	SK 50/BT 50/CAT 50	0.08



SCHUNK SE & Co. KG
Spanntechnik
Greiftechnik
Automatisierungstechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
CMS@de.schunk.com
schunk.com