


Príslušenstvo na čistenie




Technické údaje

Opis	Opis	ID	Pre upínací priemer	Hmotnosť [kg]
Zylinderbürste 6	Valcovitá kefa 6	9102002	6 mm	0.03
Zylinderbürste 8	Valcovitá kefa 8	9102003	8 mm	0.03
Zylinderbürste 10	Valcovitá kefa 10	9102004	10 mm	0.03
Zylinderbürste 12	Valcovitá kefa 12	9102005	12 mm	0.03
Zylinderbürste 16	Valcovitá kefa 16	9102017	16 mm	0.04
Zylinderbürste 20	Valcovitá kefa 20	9102007	20 mm	0.04
Zylinderbürste 25	Valcovitá kefa 25	9102009	25 mm	0.04
Zylinderbürste 32	Valcovitá kefa 32	9102016	32 mm	0.04




Technické údaje

Opis	Opis	ID	Pre upínací priemer	Hmotnosť [kg]
TK-Cleaner TKC 6	TK-Cleaner TKC 6	0280010	6 mm	0.045
TK-Cleaner TKC 8	TK-Cleaner TKC 8	0280011	8 mm	0.045
TK-Cleaner TKC 10	TK-Cleaner TKC 10	0280012	10 mm	0.045
TK-Cleaner TKC 12	TK-Cleaner TKC 12	0280013	12 mm	0.044
TK-Cleaner TKC 14	TK-Cleaner TKC 14	0280014	14 mm	0.044




Technické údaje

Opis	Opis	ID	Pre upínací priemer	Hmotnosť [kg]
TK-Cleaner TKC 16	TK-Cleaner TKC 16	0280015	16 mm	0.042
TK-Cleaner TKC 18	TK-Cleaner TKC 18	0280016	18 mm	0.044
TK-Cleaner TKC 20	TK-Cleaner TKC 20	0280017	20 mm	0.052
TK-Cleaner TKC 25	TK-Cleaner TKC 25	0280018	25 mm	0.052
TK-Cleaner TKC 32	TK-Cleaner TKC 32	0280019	32 mm	0.089
TK-Cleaner TKC 40	TK-Cleaner TKC 40	27000350	40 mm	0.09
TK-Cleaner TKC 42	TK-Cleaner TKC 42	27000351	42 mm	0.095




Technické údaje

Opis	ID	Pre rozhranie	Hmotnosť [kg]
Stierač kužeľa HSK 32	23005129	HSK 32	0.02
Stierač kužeľa HSK 40	23005130	HSK 40	0.04
Stierač kužeľa HSK 50	23005131	HSK 50	0.045
Stierač kužeľa HSK 63	23002483	HSK 63	0.05
Stierač kužeľa HSK 80	23005132	HSK 80	0.55
Stierač kužeľa HSK 100	23005133	HSK 100	0.6



Technické údaje

Opis	Ident. č.	Hmotnosť	Min./max. teplota okolia	Max. povolený počet otáčok	Max. prevádzkový tlak	Rozmery Ø D x Z
		[kg]	[°C]	[min ⁻¹]	[bar]	[mm]
RGG 20	0308590	0.1	-10 - 90	100	80	37 - 78



Technické údaje

Opis	ID	Pre rozhranie	Hmotnosť [kg]
Kuželovitý stierač SK/BT/CAT 30	0212211	SK 30/BT 30/CAT 30	0.03
Kuželovitý stierač SK/BT/CAT 40	27001419	SK 40/BT 40/CAT 40	0.063
Kuželovitý stierač SK/BT/CAT 50	27001086	SK 50/BT 50/CAT 50	0.08



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com