


Accessori per la pulizia

Spazzola cilindrica




Dati tecnici

Descrizione	Descrizione	ID	Per diametro di serraggio	Peso [kg]
Zylinderbürste 6	Spazzola di pulizia 6	9102002	6 mm	0.03
Zylinderbürste 8	Spazzola di pulizia 8	9102003	8 mm	0.03
Zylinderbürste 10	Spazzola di pulizia 10	9102004	10 mm	0.03
Zylinderbürste 12	Spazzola di pulizia 12	9102005	12 mm	0.03
Zylinderbürste 16	Spazzola di pulizia 16	9102017	16 mm	0.04
Zylinderbürste 20	Spazzola di pulizia 20	9102007	20 mm	0.04
Zylinderbürste 25	Spazzola di pulizia 25	9102009	25 mm	0.04
Zylinderbürste 32	Spazzola di pulizia 32	9102016	32 mm	0.04




Dati tecnici

Descrizione	Descrizione	ID	Per diametro di serraggio	Peso [kg]
TK-Cleaner TKC 6	TK-Cleaner TKC 6	0280010	6 mm	0.045
TK-Cleaner TKC 8	TK-Cleaner TKC 8	0280011	8 mm	0.045
TK-Cleaner TKC 10	TK-Cleaner TKC 10	0280012	10 mm	0.045
TK-Cleaner TKC 12	TK-Cleaner TKC 12	0280013	12 mm	0.044
TK-Cleaner TKC 14	TK-Cleaner TKC 14	0280014	14 mm	0.044




Dati tecnici

Descrizione	Descrizione	ID	Per diametro di serraggio	Peso [kg]
TK-Cleaner TKC 16	TK-Cleaner TKC 16	0280015	16 mm	0.042
TK-Cleaner TKC 18	TK-Cleaner TKC 18	0280016	18 mm	0.044
TK-Cleaner TKC 20	TK-Cleaner TKC 20	0280017	20 mm	0.052
TK-Cleaner TKC 25	TK-Cleaner TKC 25	0280018	25 mm	0.052
TK-Cleaner TKC 32	TK-Cleaner TKC 32	0280019	32 mm	0.089
TK-Cleaner TKC 40	TK-Cleaner TKC 40	27000350	40 mm	0.09
TK-Cleaner TKC 42	TK-Cleaner TKC 42	27000351	42 mm	0.095




Dati tecnici

Descrizione	ID	Per interfaccia	Peso [kg]
Cono pulitore HSK 32	23005129	HSK 32	0.02
Cono pulitore HSK 40	23005130	HSK 40	0.04
Cono pulitore HSK 50	23005131	HSK 50	0.045
Cono pulitore HSK 63	23002483	HSK 63	0.05
Cono pulitore HSK 80	23005132	HSK 80	0.55
Cono pulitore HSK 100	23005133	HSK 100	0.6



Dati tecnici

Descrizione	ID	Peso	Temperatura ambiente min/max	Giri/min max consentiti	Pressione di esercizio max.	Dimensioni Ø D x Z
		[kg]	[°C]	[min ⁻¹]	[bar]	[mm]
RGG 20	0308590	0.1	-10 - 90	100	80	37 - 78



Dati tecnici

Descrizione	ID	Per interfaccia	Peso [kg]
Pulitore conico SK/BT/CAT 30	0212211	SK 30/BT 30/CAT 30	0.03
Pulitore conico SK/BT/CAT 40	27001419	SK 40/BT 40/CAT 40	0.063
Pulitore conico SK/BT/CAT 50	27001086	SK 50/BT 50/CAT 50	0.08



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com