

**TOOLFIX**

Hand in hand for tomorrow



## Technické údaje

| Opis            | ID                      | Pre rozhranie                                 | Hmotnosť [kg] |
|-----------------|-------------------------|-----------------------------------------------|---------------|
| WMS-M HSK-A 32  | <a href="#">0201937</a> | HSK-A 32                                      | 3.5           |
| WMS-M HSK-A 40  | <a href="#">0201938</a> | HSK-A 40                                      | 8.2           |
| WMS-M HSK-A 50  | <a href="#">0201939</a> | HSK-A 50                                      | 8.8           |
| WMS-M HSK-A 63  | <a href="#">0201940</a> | HSK-A 63                                      | 9.7           |
| WMS-M HSK-A 80  | <a href="#">0201941</a> | HSK-A 80                                      | 10.2          |
| WMS-M HSK-A 100 | <a href="#">0201942</a> | HSK-A 100                                     | 11.8          |
| WMS-M HSK-E 32  | <a href="#">0201943</a> | HSK-E 32                                      | 8.2           |
| WMS-M HSK-E 40  | <a href="#">0201944</a> | HSK-E 40                                      | 8.2           |
| WMS-M HSK-E 50  | <a href="#">0201945</a> | HSK-E 50                                      | 8.7           |
| WMS-M HSK-E 63  | <a href="#">0201946</a> | HSK-E 63                                      | 9.5           |
| WMS-M HSK-F 63  | <a href="#">0201611</a> | HSK-F 63                                      | 9.6           |
| WMS-M CAPTO C4  | <a href="#">0201911</a> | SCHUNK CAPTO C4                               | 7.6           |
| WMS-M CAPTO C5  | <a href="#">0201913</a> | SCHUNK CAPTO C5                               | 7.6           |
| WMS-M CAPTO C6  | <a href="#">0201914</a> | SCHUNK CAPTO C6                               | 8.5           |
| WMS-M CAPTO C8  | <a href="#">1312493</a> | SCHUNK CAPTO C8                               | 3.5           |
| WMS-M VDI 25    | <a href="#">0201927</a> | VDI 25                                        | 7.7           |
| WMS-M VDI 30    | <a href="#">0201928</a> | VDI 30                                        | 7.7           |
| WMS-M VDI 40    | <a href="#">0201929</a> | VDI 40                                        | 8.6           |
| WMS-M ISO 30    | <a href="#">0201934</a> | SK 30 / BT 30 / BT-DC 30 / CAT 30             | 7.8           |
| WMS-M ISO 40    | <a href="#">0201935</a> | SK 40 / BT 40 / BT-DC 40 / CAT 40 / CAT-DC 40 | 7.9           |
| WMS-M ISO 50    | <a href="#">0201936</a> | SK 50 / BT 50 / BT-DC 50 / CAT 50             | 10            |



## Technické údaje

| Opis            | ID                      | Pre rozhranie                                 | Hmotnosť [kg] |
|-----------------|-------------------------|-----------------------------------------------|---------------|
| WMS-V HSK-A 32  | <a href="#">0201951</a> | HSK-A 32                                      | 3.5           |
| WMS-V HSK-A 40  | <a href="#">0201952</a> | HSK-A 40                                      | 3.5           |
| WMS-V HSK-A 50  | <a href="#">0201953</a> | HSK-A 50                                      | 3.5           |
| WMS-V HSK-A 63  | <a href="#">0201954</a> | HSK-A 63                                      | 4.8           |
| WMS-V HSK-A 80  | <a href="#">0201955</a> | HSK-A 80                                      | 3.5           |
| WMS-V HSK-A 100 | <a href="#">0201933</a> | HSK-A 100                                     | 2.2           |
| WMS-V HSK-E 32  | <a href="#">0201956</a> | HSK-E 32                                      | 3.5           |
| WMS-V HSK-E 40  | <a href="#">0201957</a> | HSK-E 40                                      | 3.5           |
| WMS-V HSK-E 50  | <a href="#">0201958</a> | HSK-E 50                                      | 3.5           |
| WMS-V HSK-E 63  | <a href="#">0201959</a> | HSK-E 63                                      | 3.5           |
| WMS-V HSK-F 63  | <a href="#">0201609</a> | HSK-F 63                                      | 1.1           |
| WMS-V CAPTO C3  | <a href="#">0201916</a> | SCHUNK CAPTO C3                               | 3.5           |
| WMS-V CAPTO C4  | <a href="#">0201917</a> | SCHUNK CAPTO C4                               | 3.5           |
| WMS-V CAPTO C5  | <a href="#">0201918</a> | SCHUNK CAPTO C5                               | 2.5           |
| WMS-V CAPTO C6  | <a href="#">0201919</a> | SCHUNK CAPTO C6                               | 3.1           |
| WMS-V CAPTO C8  | <a href="#">0201920</a> | SCHUNK CAPTO C8                               | 3.5           |
| WMS-V VDI 25    | <a href="#">0201966</a> | VDI 25                                        | 3.5           |
| WMS-V VDI 30    | <a href="#">0201967</a> | VDI 30                                        | 3.5           |
| WMS-V VDI 40    | <a href="#">0201968</a> | VDI 40                                        | 3.5           |
| WMS-V ISO 30    | <a href="#">0201948</a> | SK 30 / BT 30 / BT-DC 30 / CAT 30             | 3.5           |
| WMS-V ISO 40    | <a href="#">0201949</a> | SK 40 / BT 40 / BT-DC 40 / CAT 40 / CAT-DC 40 | 3.5           |
| WMS-V ISO 50    | <a href="#">0201950</a> | SK 50 / BT 50 / BT-DC 50 / CAT 50             | 5.3           |
| WMS-VB          | <a href="#">0201947</a> |                                               | 5.5           |



**SCHUNK SE & Co. KG**

**Spanntechnik**

**Greiftechnik**

**Automatisierungstechnik**

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

[CMS@de.schunk.com](mailto:CMS@de.schunk.com)

[schunk.com](http://schunk.com)