



TENDO 액세서리



기술 데이터

설명	설명	ID	중량 [kg]
TENDO GZB-S Büchsenzieher	TENDO GZB-S 슬리브 제거기	9937987	0.118



기술 데이터

설명	설명	ID	D1 [mm/Inch]	L1 [mm]	중량 [kg]
TENDO SPW Ø6	TENDO SPW Ø6	0200020	6 mm	50	0.028
TENDO SPW Ø8	TENDO SPW Ø8	0200021	8 mm	50	0.034
TENDO SPW Ø10	TENDO SPW Ø10	0200022	10 mm	80	0.049
TENDO SPW Ø12	TENDO SPW Ø12	0200023	12 mm	80	0.07
TENDO SPW Ø14	TENDO SPW Ø14	0200024	14 mm	80	0.092
TENDO SPW Ø16	TENDO SPW Ø16	0200025	16 mm	70	0.119
TENDO SPW Ø18	TENDO SPW Ø18	0200026	18 mm	70	0.148
TENDO SPW Ø20	TENDO SPW Ø20	0200027	20 mm	80	0.182
TENDO SPW Ø25	TENDO SPW Ø25	0200028	25 mm	80	0.2
TENDO SPW Ø32	TENDO SPW Ø32	0200029	32 mm	80	0.23
TENDO SPW Ø1/4"	TENDO SPW Ø1/4"	9646210	1/4"	55	0.028
TENDO SPW Ø3/8"	TENDO SPW Ø3/8"	9646211	3/8"	60	0.035
TENDO SPW Ø1/2"	TENDO SPW Ø1/2"	9646212	1/2"	65	0.05
TENDO SPW Ø5/8"	TENDO SPW Ø5/8"	9646213	5/8"	68	0.107
TENDO SPW Ø3/4"	TENDO SPW Ø3/4"	9646214	3/4"	70	0.161
TENDO SPW Ø7/8"	TENDO SPW Ø7/8"	9646215	7/8"	70	0.213
TENDO SPW Ø1"	TENDO SPW Ø1"	9646216	1"	80	0.327
TENDO SPW Ø1 1/4"	TENDO SPW Ø1 1/4"	9646217	1 1/4"	93	0.534




기술 데이터

설명	설명	ID	중량 [kg]
TENDO Aufbewahrungskoffer	TENDO 저장 박스	0200030	1




기술 데이터

설명	설명	ID	중량 [kg]
Innensechskantschlüssel SW 4x100	6각 소켓 렌치 SW 4x100	9205640	0.064
Innensechskantschlüssel SW 5x100	6각 소켓 렌치 SW 5x100	9205650	0.06
Innensechskantschlüssel SW 6x100	6각 소켓 렌치 SW 6x100	9205660	0.07
Innensechskantschlüssel SW 5x200	6각 소켓 렌치 SW 5x200	9949977	0.064
Innensechskantschlüssel SW 6x200	6각 소켓 렌치 SW 6x200	9205662	0.091



기술 데이터

설명	설명	ID	중량 [kg]
Innensechskantschlüssel SW 2.5x60	6각 소켓 렌치 SW 2.5x60	9936185	0.2



기술 데이터

설명	ID	중량 [kg]
TORX PLUS 15x80	9955034	0.01



SCHUNK SE & Co. KG
Spanntechnik
Greiftechnik
Automatisierungstechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
CMS@de.schunk.com
schunk.com