



## SINO 액세서리




## 기술 데이터

| 설명               | ID                      | 클램핑 지름용             | D1<br>[mm] | D2<br>[mm] | L1<br>[mm] | 중량<br>[kg] |
|------------------|-------------------------|---------------------|------------|------------|------------|------------|
| SINOclamp D12    | <a href="#">0210640</a> | Ø12, Ø1/2"          | 44.45      | 80         | 261        | 0.96       |
| SINOclamp D16-25 | <a href="#">0210641</a> | Ø16-Ø25, Ø3/4", Ø1" | 49.72      | 84         | 265        | 0.97       |
| SINOclamp D32    | <a href="#">0210642</a> | Ø32, Ø1 1/4"        | 69.85      | 108        | 371        | 1.19       |



기술 데이터

| 설명                         | 설명                 | ID      | 클램핑 지름용            | L1<br>[mm] | 중량<br>[kg] |
|----------------------------|--------------------|---------|--------------------|------------|------------|
| SINO Hakenschlüssel D12-25 | SINO 스패너 렌치 D12-25 | 0208877 | Ø12-Ø25, Ø1/2"-Ø1" | 367        | 0.428      |
| SINO Hakenschlüssel D32    | SINO 스패너 렌치 D32    | 0208879 | Ø32, Ø1 1/4"       | 403        | 0.338      |



기술 데이터

| 설명      | ID      | 중량<br>[kg] |
|---------|---------|------------|
| SINOmax | 0208840 | 0.14       |





**SCHUNK SE & Co. KG**  
**Spanntechnik**  
**Greiftechnik**  
**Automatisierungstechnik**

Bahnhofstr. 106 - 134  
D-74348 Lauffen/Neckar  
Tel. +49-7133-103-0  
Fax +49-7133-103-2399  
CMS@de.schunk.com  
schunk.com