



Príslušenstvo SIN0




Technické údaje

Opis	ID	Pre upínací priemer	D1 [mm]	D2 [mm]	L1 [mm]	Hmotnosť [kg]
SINOclamp D12	0210640	Ø12, Ø1/2"	44.45	80	261	0.96
SINOclamp D16-25	0210641	Ø16-Ø25, Ø3/4", Ø1"	49.72	84	265	0.97
SINOclamp D32	0210642	Ø32, Ø1 1/4"	69.85	108	371	1.19



Technické údaje

Opis	Opis	ID	Pre upínací priemer	L1 [mm]	Hmotnosť [kg]
SINO Hakenschlüssel D12-25	Hákový kľúč SINO D12-25	0208877	Ø12-Ø25, Ø1/2"-Ø1"	367	0.428
SINO Hakenschlüssel D32	Hákový kľúč SINO D32	0208879	Ø32, Ø1 1/4"	403	0.338



Technické údaje

Opis	ID	Hmotnosť [kg]
SIN0max	0208840	0.14



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

CMS@de.schunk.com

schunk.com