



TRIBOS SVP




기술 데이터

설명	ID	중량 [kg]
TRIBOS SVP-2	0211760	39



기술 데이터

설명	ID	중량 [kg]	주 전압
TRIBOS SVP-2D	0211762	41.5	90 - 264 V



기술 데이터

설명	ID	중량 [kg]	주 전압
TRIBOS SVP-5	1612996	145	400 V




기술 데이터

설명	ID	중량 [kg]
TRIBOS SVP-2D/2D-H Scanner	0201756	0.6



기술 데이터

설명	ID	중량 [kg]
TRIBOS SVP-2D/2D-H Fixscanner I	0201754	0.4
TRIBOS SVP-2D/2D-H Fixscanner II	0201755	0.025



기술 데이터

설명	ID	B 너비 [mm]	높이 H [mm]	길이 T [mm]	중량 [kg]
TRIBOS SVP-M	0211768	260	190	390	8.9




기술 데이터

설명	ID	중량 [kg]
TRIBOS SVP-M Cover	9937963	0.005




기술 데이터

설명	ID	중량 [kg]
TRIBOS SVP-2/SVP-2D Cover	9935548	0.2




기술 데이터

설명	ID	중량 [kg]
TRIBOS-Mini SVP Ø6.65	1357071	0.7
TRIBOS-Mini SVP Ø9	0211763	0.7



기술 데이터

설명	ID	중량 [kg]
TRIBOS-RM SVP Ø14	1346220	1.95
TRIBOS-RM SVP Ø18	1357074	1.95
TRIBOS-RM SVP Ø20	0211764	5.6



기술 데이터

설명	설명	ID	중량 [kg]
TRIBOS-RM/-Mini SVP Montagevorrichtung	TRIBOS-RM/-Mini SVP 조립 디바이스	9954724	0.829



기술 데이터

설명	ID	중량 [kg]
TRIBOS LMG-M	0201961	1.24



SCHUNK SE & Co. KG
Spanntechnik
Greiftechnik
Automatisierungstechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
CMS@de.schunk.com
schunk.com