




Superior Clamping and Gripping



Product Information

Connecting element PAM

Loadable. Easy assembly. Robust.

Connecting elements PAM

Standard elements and adapters for the accurately repeatable connections of PowerCube modules

Field of application


for simple and repeatable connection of all PowerCube modules

Advantages – Your benefits

Standard elements for high availability

Geometry "straight", "conical" and "angular" for maximum combinations

Suitable for all grippers, swivel units, drives and linear modules of the PowerCube series



Options and special information

Precise: due to the use of SCHUNK ZHU centering sleeves

Applications



① Connecting element PAM

② PR universal rotary unit

③ Universal gripper PG

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Universal gripper PG



Rotary module PR,
electric




PW electrical rotary
pan-tilt actuator

① For more information on these products can be found on the following product pages or at schunk.com.


PAM straight

Connecting element



Description	PAM 100	PAM 101	PAM 102	PAM 103	PAM 104	PAM 105
ID	0307800	0307801	0307802	0307803	0307804	0307805
Dimensions	70x70/35/70x70 mm	70x70/70/70x70 mm	90x90/45/90x90 mm	90x90/90/90x90 mm	110x110/55/110x110 mm	110x110/110/110x110 mm


PAM 100 – straight



72 Fit for centering sleeves

Suitable for the mechatronic modules PG, PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the size 70


PAM 101 – straight



72 Fit for centering sleeves

Suitable for the mechatronic modules PG, PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the size 70


PAM 102 – straight



72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the size 90.

PAM 103 – straight




72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the size 90.

PAM straight

Connecting element


PAM 104 – straight



72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 110.

PAM 105 – straight




72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 110.


PAM conical

Connecting element



Description	PAM 110	PAM 111	PAM 112	PAM 113
ID	0307810	0307811	0307812	0307813
Dimensions	90x90/45/70x70 mm	90x90/90/70x70 mm	110x110/55/90x90 mm	110x110/110/90x90 mm


PAM 110 – conical



72 Fit for centering sleeves

Suitable for the mechatronic modules PG, PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 70/90.


PAM 111 – conical



72 Fit for centering sleeves

Suitable for the mechatronic modules PG, PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 70/90.


PAM 112 – conical



72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 90/110.

PAM 113 – conical




72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 90/110.


PAM angle

Connecting element



Description	PAM 120	PAM 121	PAM 122
ID	0307820	0307821	0307822
Dimensions	70,5x70,5/98/70x70 mm	90,5x90,5//122x122 mm	110,5x110,5//146x146 mm


PAM 120 - angle



72 Fit for centering sleeves

Suitable for the mechatronic modules PG, PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the size 70


PAM 121 - angle



72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the size 90.

PAM 122 - angle



72 Fit for centering sleeves

Suitable for the mechatronic modules PW-V5, PW-V6, PR, PR2, PDU, PDU2, PSM and PSM2 of the sizes 110.



SCHUNK GmbH & Co. KG
Spann- und Greiftechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
info@de.schunk.com
schunk.com

Folgen Sie uns | *Follow us*

