

## Range of machines - DOOSAN



| machine manufacturer | machine type             | Lathe chuck / type     | packet Id-no. |
|----------------------|--------------------------|------------------------|---------------|
| DOOSAN               | PUMA 2600 SY GSP A5      | ROTA NCK plus 165 Z140 | 88032715      |
| DOOSAN               | PUMA 2100 SY GSP A5      | ROTA NCK plus 165 Z140 | 88032715      |
| DOOSAN               | Lynx 220 A HSP A5        | ROTA NCK plus 165 Z140 | 88033010      |
| DOOSAN               | Lynx 220 LM HSP A5       | ROTA NC plus 185 Z140  | 88033016      |
| DOOSAN               | Lynx 220 B HSP A6        | ROTA NC plus 185 Z140  | 88033014      |
| DOOSAN               | TT 1800 SY HSP/GSP A6    | ROTA NC plus 215 Z170  | 88032709      |
| DOOSAN               | MX 2100 HSP/GSP A6       | ROTA NC plus 215 Z170  | 88032709      |
| DOOSAN               | PUMA 2100 SY HSP A6      | ROTA NC plus 215 Z170  | 88032709      |
| DOOSAN               | Lynx 220 C HSP A6        | ROTA NC plus 215 Z170  | 88033015      |
| DOOSAN               | PUMA 26 00 SY HSP A8     | ROTA NC plus 260 Z220  | 88032712      |
| DOOSAN               | PUMA MX 26 00 HSP/GSP A8 | ROTA NC plus 260 Z220  | 88032796      |
| DOOSAN               | PUMA 3100 HSP A11        | ROTA NC plus 315 Z220  | 88032805      |
| DOOSAN               | TT 1800 SY HSP/GSP A6    | ROTA THW plus 215 Z170 | 88032711      |
| DOOSAN               | MX 2100 HSP/GSP A6       | ROTA THW plus 215 Z170 | 88032711      |
| DOOSAN               | PUMA 2100 SY HSP A6      | ROTA THW plus 215 Z170 | 88032711      |
| DOOSAN               | Lynx 220 C HSP A6        | ROTA THW plus 215 Z170 | 88033011      |
| DOOSAN               | PUMA 2600 SY HSP A8      | ROTA THW plus 260 Z220 | 88032782      |
| DOOSAN               | PUMA MX 26 00 HSP/GSP A8 | ROTA THW plus 260 Z220 | 88032795      |
| DOOSAN               | PUMA 3100 HSP A11        | ROTA THW plus 315 Z220 | 88032806      |
| DOOSAN               | PUMA 400 B A11           | ROTA THW 400 Z300      | 88032783      |
| DOOSAN               | PUMA 400 C A15           | ROTA THW 500 Z380      | 88032788      |
| DOOSAN               | PUMA 480 A15             | ROTA THW 500 Z380      | 88032788      |
| DOOSAN               | PUMA 700 TYP1 A15        | ROTA THW 630 Z520      | 88032790      |
| DOOSAN               | PUMA 400 B A11           | ROTA NC 400 Z300       | 88032784      |
| DOOSAN               | PUMA 400 C A15           | ROTA NC 500 Z380       | 88032786      |
| DOOSAN               | PUMA 480 A15             | ROTA NC 500 Z380       | 88032786      |
| DOOSAN               | PUMA 700 TYP1 A15        | ROTA NC 630 Z520       | 88032791      |

**Additional:** Information is subject to change. In case of order, please send a drawing of the machine spindle for examination of the compatibility.