



Tendo SDF EC BT50 Ø12 :

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF EC BT50 Ø12	206444	69	BT 50	direkt	186
ZB	207911			GZB-S Ø12/04 KD	7
ZB	207912			GZB-S Ø12/05 KD	12
ZB	207913			GZB-S Ø12/06 KD	31
ZB	207915			GZB-S Ø12/08 KD	44



Tendo SDF KS JIS BT40 Ø12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF KS JIS BT40 Ø12	204443	90	BT 40	direkt	155
ZB	207911			GZB-S Ø12/04 KD	7
ZB	207912			GZB-S Ø12/05 KD	12
ZB	207913			GZB-S Ø12/06 KD	31
ZB	207915			GZB-S Ø12/08 KD	43



Tendo SDF LSS Ø12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF LSS Ø12	204534	200	HSK A63	direkt	71
ZB	207911			GZB-S Ø12/04 KD	<5
ZB	207912			GZB-S Ø12/05 KD	<5
ZB	207913			GZB-S Ø12/06 KD	10
ZB	207915			GZB-S Ø12/08 KD	25



Tendo SDF EC Ø12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF EC Ø12	206404	80	HSK A63	direkt	155
ZB	207911			GZB-S Ø12/04 KD	7
ZB	207912			GZB-S Ø12/05 KD	10
ZB	207913			GZB-S Ø12/06 KD	28
ZB	207915			GZB-S Ø12/08 KD	45



Tendo classic SDF Ø12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF Ø12	204054	85	HSK A63	direkt	139
ZB	207911			GZB-S Ø12/04 KD	7
ZB	207912			GZB-S Ø12/05 KD	10
ZB	207913			GZB-S Ø12/06 KD	30
ZB	207915			GZB-S Ø12/08 KD	46



Tendo Turn DKE Ø25-12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
Tendo Turn DKE Ø25-12	216353			direkt	124
ZB	207911			GZB-S Ø12/04 KD	7
ZB	207912			GZB-S Ø12/05 KD	11
ZB	207913			GZB-S Ø12/06 KD	28
ZB	207915			GZB-S Ø12/08 KD	38

Tendo Turn DKE Ø25-12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
Tendo Turn DKE Ø25-12	216353			direkt	149
ZB	207911			GZB-S Ø12/04 KD	7
ZB	207912			GZB-S Ø12/05 KD	12
ZB	207913			GZB-S Ø12/06 KD	29
ZB	207915			GZB-S Ø12/08 KD	39

**Tendo SDF LSS Ø20:**

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF LSS Ø20	204536	200	HSK-A63	direkt	204
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	7
ZB	207923			GZB-S Ø20/06 KD	21
ZB	207924			GZB-S Ø20/07 KD	27
ZB	207925			GZB-S Ø20/08 KD	33
ZB	207926			GZB-S Ø20/09 KD	34
ZB	207927			GZB-S Ø20/10 KD	55
ZB	207928			GZB-S Ø20/11 KD	71
ZB	207929			GZB-S Ø20/12 KD	100
ZB	207930			GZB-S Ø20/13 KD	73
ZB	207931			GZB-S Ø20/14 KD	119
ZB	207932			GZB-S Ø20/15 KD	70
ZB	207933			GZB-S Ø20/16 KD	113

**Tendo SDF EC BT 50 Ø20:**

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF EC BT50 Ø20	206446	83,5	BT 50	direkt	514
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	16
ZB	207923			GZB-S Ø20/06 KD	39
ZB	207924			GZB-S Ø20/07 KD	54
ZB	207925			GZB-S Ø20/08 KD	66
ZB	207926			GZB-S Ø20/09 KD	76
ZB	207927			GZB-S Ø20/10 KD	131
ZB	207928			GZB-S Ø20/11 KD	131
ZB	207929			GZB-S Ø20/12 KD	181
ZB	207930			GZB-S Ø20/13 KD	182
ZB	207931			GZB-S Ø20/14 KD	261
ZB	207932			GZB-S Ø20/15 KD	187
ZB	207933			GZB-S Ø20/16 KD	276

**Tendo SDF WZS SK50 Ø20:**

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF WZS SK50 Ø20	219226	110	SK 50	direkt	185
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	7
ZB	207923			GZB-S Ø20/06 KD	21
ZB	207924			GZB-S Ø20/07 KD	25
ZB	207925			GZB-S Ø20/08 KD	27
ZB	207926			GZB-S Ø20/09 KD	30
ZB	207927			GZB-S Ø20/10 KD	49
ZB	207928			GZB-S Ø20/11 KD	53
ZB	207929			GZB-S Ø20/12 KD	87
ZB	207930			GZB-S Ø20/13 KD	68
ZB	207931			GZB-S Ø20/14 KD	108
ZB	207932			GZB-S Ø20/15 KD	68
ZB	207933			GZB-S Ø20/16 KD	110



Tendo SDF KS SK50 Ø20:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF KS SK50 Ø20	204246	80,5	SK 50	direkt	410
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	20
ZB	207923			GZB-S Ø20/06 KD	34
ZB	207924			GZB-S Ø20/07 KD	58
ZB	207925			GZB-S Ø20/08 KD	86
ZB	207926			GZB-S Ø20/09 KD	87
ZB	207927			GZB-S Ø20/10 KD	129
ZB	207928			GZB-S Ø20/11 KD	141
ZB	207929			GZB-S Ø20/12 KD	220
ZB	207930			GZB-S Ø20/13 KD	205
ZB	207931			GZB-S Ø20/14 KD	280
ZB	207932			GZB-S Ø20/15 KD	223
ZB	207933			GZB-S Ø20/16 KD	309



Tendo SDF EC Ø20:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF EC Ø20	206406	80	HSK-A63	direkt	520
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	15
ZB	207923			GZB-S Ø20/06 KD	41
ZB	207924			GZB-S Ø20/07 KD	48
ZB	207925			GZB-S Ø20/08 KD	63
ZB	207926			GZB-S Ø20/09 KD	67
ZB	207927			GZB-S Ø20/10 KD	104
ZB	207928			GZB-S Ø20/11 KD	118
ZB	207929			GZB-S Ø20/12 KD	172
ZB	207930			GZB-S Ø20/13 KD	155
ZB	207931			GZB-S Ø20/14 KD	250
ZB	207932			GZB-S Ø20/15 KD	165
ZB	207933			GZB-S Ø20/16 KD	248



Tendo SDF classic Ø20:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF classic Ø20	204056	90	HSK-A63	direkt	502
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	19
ZB	207923			GZB-S Ø20/06 KD	39
ZB	207924			GZB-S Ø20/07 KD	51
ZB	207925			GZB-S Ø20/08 KD	77
ZB	207926			GZB-S Ø20/09 KD	76
ZB	207927			GZB-S Ø20/10 KD	129
ZB	207928			GZB-S Ø20/11 KD	130
ZB	207929			GZB-S Ø20/12 KD	173
ZB	207930			GZB-S Ø20/13 KD	184
ZB	207931			GZB-S Ø20/14 KD	250
ZB	207932			GZB-S Ø20/15 KD	196
ZB	207933			GZB-S Ø20/16 KD	271



Tendo SDF SVL-150-20 Ø20:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF SVL-150- 20 Ø20	206306	150		direkt	421
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	21
ZB	207923			GZB-S Ø20/06 KD	40
ZB	207924			GZB-S Ø20/07 KD	52
ZB	207925			GZB-S Ø20/08 KD	73
ZB	207926			GZB-S Ø20/09 KD	80
ZB	207927			GZB-S Ø20/10 KD	130
ZB	207928			GZB-S Ø20/11 KD	131
ZB	207929			GZB-S Ø20/12 KD	178
ZB	207930			GZB-S Ø20/13 KD	187
ZB	207931			GZB-S Ø20/14 KD	233
ZB	207932			GZB-S Ø20/15 KD	192
ZB	207933			GZB-S Ø20/16 KD	285



Tendo SDF SVL-150-20 Ø12:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF SVL-150- 20 Ø12	206304	150		direkt	132
ZB	207911			GZB-S Ø12/04 KD	6
ZB	207912			GZB-S Ø12/05 KD	9
ZB	207913			GZB-S Ø12/06 KD	21
ZB	207915			GZB-S Ø12/08 KD	29



Tendo SDF HSK-A63 Ø25:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF HSK-A63 Ø25	204057	120	HSK-A63	direkt	409
ZB	207865			GZB-S Ø25/06 KD	26
ZB	207866			GZB-S Ø25/08 KD	38
ZB	207867			GZB-S Ø25/010 KD	63
ZB	207868			GZB-S Ø25/012 KD	125
ZB	207869			GZB-S Ø25/014 KD	145
ZB	207870			GZB-S Ø25/016 KD	194
ZB	207871			GZB-S Ø25/018 KD	239
ZB	207872			GZB-S Ø25/020 KD	266



Tendo SDF HSK-A100 Ø25:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF HSK- A100 Ø25	204067	110	HSK-A100	direkt	426
ZB	207865			GZB-S Ø25/06 KD	29
ZB	207866			GZB-S Ø25/08 KD	42
ZB	207867			GZB-S Ø25/010 KD	67
ZB	207868			GZB-S Ø25/012 KD	143
ZB	207869			GZB-S Ø25/014 KD	150
ZB	207870			GZB-S Ø25/016 KD	210
ZB	207871			GZB-S Ø25/018 KD	251
ZB	207872			GZB-S Ø25/020 KD	292



Tendo SDF HSK-A63 Ø32:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF HSK-A63 Ø32	204058	125	HSK-A63	direkt	726
ZB	207940			GZB-S Ø32/06 KD	39
ZB	207941			GZB-S Ø32/08 KD	62
ZB	207942			GZB-S Ø32/010 KD	112
ZB	207943			GZB-S Ø32/012 KD	174
ZB	207944			GZB-S Ø32/014 KD	159
ZB	207945			GZB-S Ø32/016 KD	308
ZB	207947			GZB-S Ø32/020 KD	372
ZB	207948			GZB-S Ø32/025 KD	479



Tendo SDF-SVL 150-32 Ø20:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF-SVL 150- 32 Ø20	206316	150		direkt	456
ZB	207920			GZB-S Ø20/3 KD	<5
ZB	207922			GZB-S Ø20/5 KD	17
ZB	207923			GZB-S Ø20/6 KD	38
ZB	207924			GZB-S Ø20/7 KD	54
ZB	207925			GZB-S Ø20/8 KD	67
ZB	207926			GZB-S Ø20/9 KD	73
ZB	207927			GZB-S Ø20/10 KD	109
ZB	207928			GZB-S Ø20/11 KD	127
ZB	207929			GZB-S Ø20/12 KD	182
ZB	207930			GZB-S Ø20/13 KD	156
ZB	207931			GZB-S Ø20/14 KD	246
ZB	207932			GZB-S Ø20/15 KD	187
ZB	207933			GZB-S Ø20/16 KD	246



Tendo SDF-KS JIS BT40 Ø32:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF-KS JIS BT40 Ø32	204465	83	JIS BT-40	direkt	818
ZB	207940			GZB-S Ø32/06 KD	38
ZB	207941			GZB-S Ø32/08 KD	60
ZB	207942			GZB-S Ø32/010 KD	110
ZB	207943			GZB-S Ø32/012 KD	162
ZB	207944			GZB-S Ø32/014 KD	160
ZB	207945			GZB-S Ø32/016 KD	284
ZB	207947			GZB-S Ø32/020 KD	368
ZB	207948			GZB-S Ø32/025 KD	491



Tendo SDF WZS SK 50 Ø32:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF WZS SK50 Ø32	219228	110	SK 50	direkt	589
ZB	207940			GZB-S Ø32/06 KD	29
ZB	207941			GZB-S Ø32/08 KD	41
ZB	207942			GZB-S Ø32/010 KD	79
ZB	207943			GZB-S Ø32/012 KD	112
ZB	207944			GZB-S Ø32/014 KD	111
ZB	207945			GZB-S Ø32/016 KD	202
ZB	207947			GZB-S Ø32/020 KD	249
ZB	207948			GZB-S Ø32/025 KD	329



Tendo SDF EC SK50 Ø32:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF EC SK50 Ø32	206428	81	SK 50	direkt	917
ZB	207940			GZB-S Ø32/06 KD	38
ZB	207941			GZB-S Ø32/08 KD	59
ZB	207942			GZB-S Ø32/010 KD	115
ZB	207943			GZB-S Ø32/012 KD	157
ZB	207944			GZB-S Ø32/014 KD	163
ZB	207945			GZB-S Ø32/016 KD	297
ZB	207947			GZB-S Ø32/020 KD	369
ZB	207948			GZB-S Ø32/025 KD	503



Tendo SDF EC Ø20, Kontrollmessung wg. Glättung der ZB:

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF EC Ø20	206406	80	HSK-A63	direkt	515
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	16
ZB	207923			GZB-S Ø20/06 KD	39
ZB	207924			GZB-S Ø20/07 KD	43
ZB	207925			GZB-S Ø20/08 KD	59
ZB	207926			GZB-S Ø20/09 KD	71
ZB	207927			GZB-S Ø20/010 KD	110
ZB	207928			GZB-S Ø20/011 KD	123
ZB	207929			GZB-S Ø20/012 KD	Bolzen wurde gewechselt.
ZB	207930			GZB-S Ø20/013 KD	161
ZB	207931			GZB-S Ø20/014 KD	235
ZB	207932			GZB-S Ø20/015 KD	186
ZB	207933			GZB-S Ø20/016 KD	221



Tendo SDF classic Ø20, Kontrollmessung mit Referenzfutter - weniger DM

Bezeichnung	ID. Nr.	L1 Maß/mm	Schnittstelle	Zwischenbüchse	Drehmoment/Nm
SDF classic Ø20	204056	90	HSK-A63	direkt	372
ZB	207920			GZB-S Ø20/03 KD	<5
ZB	207922			GZB-S Ø20/05 KD	22
ZB	207923			GZB-S Ø20/06 KD	38
ZB	207924			GZB-S Ø20/07 KD	50
ZB	207925			GZB-S Ø20/08 KD	71
ZB	207926			GZB-S Ø20/09 KD	83
ZB	207927			GZB-S Ø20/010 KD	124
ZB	207928			GZB-S Ø20/011 KD	131
ZB	207929			GZB-S Ø20/012 KD	185
ZB	207930			GZB-S Ø20/013 KD	187
ZB	207931			GZB-S Ø20/014 KD	250
ZB	207932			GZB-S Ø20/015 KD	214
ZB	207933			GZB-S Ø20/016 KD	245