




DPG-plus ____-1-V-HD

Washing parts in the cleaning area, deburring water jet


Your advantages and benefits

- Special coating on all internal steel parts to prevent rusting
- Additional wipers and enlarged grease reserves
- Complete internally sealed sensor system
- Central connection of the sensor system and air supply of the gripper
 - On the underside via distributor housing
 - Sealing through customer PG fittings.
- All external screws and set-screws from stainless steel (exception: fastening screw intermediate jaw)
- Special magnetic sensor with reduced temperature sensitivity
- Special coating of the entire gripper black anodized
- Same dimensions of the gripper in the basic and AS-, IS- version

Please contact us with your individual requirement.
You can reach the Team Gripping systems at:

Technical Hotline +49-7133-103-2696
E-mail: automationsolution@de.schunk.com

DPG-plus 125-1-V-HD
DPG-plus 125-1-AS-V-HD
DPG-plus 125-1-IS-V-HD



A, a Main, direct connection
Opens gripper

S, s Air purge connection

B, b Main, direct connection
Closes gripper


90 Alternative connection possibility

Technical data

Technical data additional technical data to basic module

- Stroke per jaw 13 mm
- Weight 3.9 kg

DPG-plus 200-1-V-HD
DPG-plus 200-1-AS-V-HD
DPG-plus 200-1-IS-V-HD



A, a Main, direct connection
Opens gripper

S, s Air purge connection

B, b Main, direct connection
Closes gripper


90 Alternative connection possibility

Technical data

Technical data additional technical data to basic module

- Stroke per jaw 25 mm
- Weight 12.87 kg

DPG-plus 300-1-V-HD
DPG-plus 300-1-AS-V-HD
DPG-plus 300-1-IS-V-HD



A, a Main, direct connection
Opens gripper

S, s Air purge connection

B, b Main, direct connection
Closes gripper

90 Alternative connection possibility

Technical data

Technical data additional technical data to basic module

- Stroke per jaw 13 mm
- Weight 3.9 kg



J. Lehmann

Jens Lehmann, deutsche Torwartlegende,
seit 2012 SCHUNK-Markenbotschafter
für sicheres, präzises Greifen und Halten.
schunk.com/Lehmann

SCHUNK GmbH & Co. KG
Spann- und Greiftechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
info@de.schunk.com

schunk.com
[youtube.com/schunkhq](https://www.youtube.com/schunkhq)
twitter.com/schunk_hq
[facebook.com/schunk.hq](https://www.facebook.com/schunk.hq)
schunk.com/lehmann



Reg. No. 003496 QM08