



Hand in hand for tomorrow



Product data sheet

Feed-through modules C0B P3

Compact. Reliable. Flexible.

Optional modules COB

Optional modules for feeding through different media such as electrical signals, pneumatics, fluids and vacuum.

Field of application

For fast media transfer with short change-over times between change master and change adapter in order to supply the end effector with the required media.

Advantages – Your benefits

Compact design Ensures a low interfering contour

Wide range of different variants for feeding through of various media

Standardized screw connection Enables quick and easy mounting on SCHUNK tool changers

Combination of several optional modules for maximum flexibility of the tool changer

Sophisticated design Ensures a combination of reliability and durability

Customer-specific designs available on request the suitable solution for any application

Cable connector, cable extensions and protection covers available on request for a comprehensive complete solution from one source



Application example



① Automatic tool changers CPB

② Optional modules COB

③ 2-finger parallel gripper PGN-plus-P

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Tool changer



Manual change system



Pallet change system

① For more information on these products can be found on the following product pages or at schunk.com.




Technical data

Description		COB P3-K	COB P3-A
ID		1607012	1607014
Suitable on		Change head	Tool
Screw connection diagram		B	B
Transmission type		Servo	Servo
Weight	[kg]	0.17	0.17
Min./max. ambient temperature	[°C]	5/60	5/60
Protection class IP		IP64 (only in a coupled state)	IP64 (only in a coupled state)
Number of pin contacts		9	9
Nominal current	[A]	3.5	3.5
Alternating voltage	[V AC]	160	160
Direct voltage	[V DC]	160	160
Electrical connection		M23 connector, 12-pin	M23 socket, 12-pin
Outlet connection		radial	radial
Special properties		Four twisted wire pairs, shielding of connector housing is via pinblock.	Four twisted wire pairs, shielding of connector housing is via pinblock.

① We recommend using the appropriate connection cables and cable extensions on the following pages for interfering-contour-optimized application.

Pin assignment for COB P3-K and COB P3-A



90 JAE interface

⑨1 Connector/angled socket

Other cable lengths on request.

Description	ID	
Straight cable connector		
KAS-12G-A-0	1344402	
KAS-12G-K-0	1344401	



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

info@de.schunk.com

schunk.com

Folgen Sie uns | *Follow us*

