



TRIBOS SRE




技术参数

| 描述              | ID                      | 用于夹持直径                          | D2<br>[mm] | L1<br>[mm] | 重量<br>[kg] | 小号备用环                   | 大号备用环                   |
|-----------------|-------------------------|---------------------------------|------------|------------|------------|-------------------------|-------------------------|
| TRIBOS-R SRE 25 | <a href="#">0201978</a> | Ø6                              | 25         | 35         | 0.735      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-R SRE 28 | <a href="#">0201980</a> | Ø8, Ø1/4"                       | 28         | 35         | 0.699      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-R SRE 35 | <a href="#">0201982</a> | Ø10, Ø3/8"                      | 35         | 40         | 0.641      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-R SRE 42 | <a href="#">0201983</a> | Ø12                             | 42         | 45         | 0.555      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-R SRE 48 | <a href="#">0201984</a> | Ø14-Ø20, Ø1/2",<br>Ø5/8", Ø3/4" | 48         | 45         | 0.658      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-R SRE 60 | <a href="#">0201921</a> | Ø25, Ø1"                        | 60         | 45         | 0.319      | <a href="#">9942628</a> | <a href="#">7008661</a> |
| TRIBOS-R SRE 67 | <a href="#">0201922</a> | Ø32, Ø1 1/4"                    | 67         | 45         | 0.212      | <a href="#">9942628</a> | <a href="#">7008661</a> |




## 技术参数

| 描述               | ID                      | 用于夹持直径 | D2<br>[mm] | L1<br>[mm] | 重量<br>[kg] | 小号备用环                   | 大号备用环                   |
|------------------|-------------------------|--------|------------|------------|------------|-------------------------|-------------------------|
| TRIBOS-RM SRE 20 | <a href="#">0201892</a> | Ø3-Ø12 | 20         | 27.2       | 0.871      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-RM SRE 25 | <a href="#">0201893</a> | Ø3-Ø6  | 25         | 35         | 0.5        | <a href="#">9936839</a> | <a href="#">9936840</a> |




技术参数

| 描述                | ID                      | 用于夹持直径       | D2<br>[mm] | L1<br>[mm] | 重量<br>[kg] | 小号备用环                   | 大号备用环                   |
|-------------------|-------------------------|--------------|------------|------------|------------|-------------------------|-------------------------|
| TRIBOS-S SRE 10   | <a href="#">0201972</a> | Ø6           | 10         | 35         | 0.915      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 10.3 | <a href="#">0201988</a> | Ø1/4"        | 10.3       | 35         | 0.5        | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 13   | <a href="#">0201973</a> | Ø8, Ø5/16"   | 13         | 35         | 0.878      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 15   | <a href="#">0201989</a> | Ø3/8"        | 15         | 45         | 0.45       | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 16   | <a href="#">0201974</a> | Ø10          | 16         | 40         | 0.895      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 17.8 | <a href="#">0201990</a> | Ø7/16"       | 17.8       | 45         | 0.4        | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 19   | <a href="#">0201975</a> | Ø12          | 19         | 45         | 0.91       | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 20   | <a href="#">0201991</a> | Ø1/2"        | 20         | 45         | 0.4        | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 22   | <a href="#">0201976</a> | Ø14          | 22         | 45         | 0.86       | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 25   | <a href="#">0201977</a> | Ø16, Ø5/8"   | 25         | 45         | 0.815      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 28   | <a href="#">0201979</a> | Ø18          | 28         | 45         | 0.769      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 29   | <a href="#">0201992</a> | Ø3/4"        | 29         | 45         | 0.35       | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 30   | <a href="#">0201981</a> | Ø20          | 30         | 45         | 0.737      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 36   | <a href="#">0201987</a> | Ø25          | 36         | 45         | 0.645      | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 36.5 | <a href="#">0201993</a> | Ø1"          | 36.5       | 45         | 0.35       | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-S SRE 45   | <a href="#">0201998</a> | Ø32, Ø1 1/4" | 45         | 45         | 0.506      | <a href="#">9936839</a> | <a href="#">9936840</a> |




## 技术参数

| 描述                   | ID                       | 用于夹持直径                    | D2<br>[mm] | L1<br>[mm] | 重量<br>[kg] | 小号备用环                   | 大号备用环                   |
|----------------------|--------------------------|---------------------------|------------|------------|------------|-------------------------|-------------------------|
| TRIBOS-Mini SRE 6.65 | <a href="#">25005968</a> | Ø1-Ø4, Ø1/8",<br>Ø3/16"   | 6.65       | 17.5       | 0.8        | <a href="#">9936839</a> | <a href="#">9936840</a> |
| TRIBOS-Mini SRE 9    | <a href="#">0201971</a>  | Ø0.3-Ø6, Ø1/8",<br>Ø3/16" | 9          | 22.5       | 0.743      | <a href="#">9936839</a> | <a href="#">9936840</a> |



技术参数

| 描述                 | ID                       | 用于夹持直径                          | D2<br>[mm] | L1<br>[mm] | 重量<br>[kg] | 小号备用环                   | 大号备用环                   |
|--------------------|--------------------------|---------------------------------|------------|------------|------------|-------------------------|-------------------------|
| TRIBOS-R SRE SO 25 | <a href="#">25000593</a> | Ø6                              | 25         | 45         | 0.5        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-R SRE SO 28 | <a href="#">25000594</a> | Ø8, Ø1/4"                       | 28         | 45         | 0.45       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-R SRE SO 48 | <a href="#">25000596</a> | Ø14-Ø20, Ø1/2",<br>Ø5/8", Ø3/4" | 48         | 45         | 0.3        | <a href="#">9938251</a> | <a href="#">9938252</a> |



## 技术参数

| 描述                   | ID                       | 用于夹持直径       | D2<br>[mm] | L1<br>[mm] | 重量<br>[kg] | 小号备用环                   | 大号备用环                   |
|----------------------|--------------------------|--------------|------------|------------|------------|-------------------------|-------------------------|
| TRIBOS-S SRE S0 10   | <a href="#">0206081</a>  | Ø6           | 10         | 35         | 0.65       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 10.3 | <a href="#">25001067</a> | Ø1/4"        | 10.3       | 45         | 0.5        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 13   | <a href="#">0206082</a>  | Ø8, Ø5/16"   | 13         | 35         | 0.35       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 15   | <a href="#">25000996</a> | Ø3/8"        | 15         | 45         | 0.3        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 16   | <a href="#">0206083</a>  | Ø10          | 16         | 40         | 0.35       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 19   | <a href="#">0206084</a>  | Ø12          | 19         | 45         | 0.4        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 20   | <a href="#">25000910</a> | Ø1/2"        | 20         | 45         | 0.3        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 22   | <a href="#">0206085</a>  | Ø14          | 22         | 45         | 0.35       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 25   | <a href="#">0206086</a>  | Ø16, Ø5/8"   | 25         | 45         | 0.3        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 28   | <a href="#">0206087</a>  | Ø18          | 28         | 45         | 0.35       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 29   | <a href="#">25001026</a> | Ø3/4"        | 29         | 45         | 0.3        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 30   | <a href="#">0206088</a>  | Ø20          | 30         | 45         | 0.35       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 35   | <a href="#">0206089</a>  | Ø25          | 35         | 45         | 0.4        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 36   | <a href="#">0206090</a>  | Ø25          | 36         | 45         | 0.32       | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 36.5 | <a href="#">25001684</a> | Ø1"          | 36.5       | 45         | 0.8        | <a href="#">9938251</a> | <a href="#">9938252</a> |
| TRIBOS-S SRE S0 45   | <a href="#">0206091</a>  | Ø32, Ø1 1/4" | 45         | 45         | 0.32       | <a href="#">9938251</a> | <a href="#">9938252</a> |



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 – 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

[CMS@de.schunk.com](mailto:CMS@de.schunk.com)

[schunk.com](http://schunk.com)