









- NOTES:**
- Preliminary Specifications:
 - Suggested Payload Limit: 100 lbs
 - Pneumatic Pass Through: (6) 1/8" NPT
 - Unit Features (2) additional module mounting flats
 - Unit Features ISO 80 Mounting Patterns on Both Sides, and a 56mm Pattern on Master

NOTES: UNLESS OTHERWISE SPECIFIED
DO NOT SCALE DRAWING.
DRAWN IN SOLIDWORKS.
ALL DIMENSIONS ARE IN MILLIMETERS.



1031 Goodworth Drive, Apex, NC 27539, USA
Tel: +1.919.772.0115 Email: info@ati-ia.com
Fax: +1.919.772.8259 www.ati-ia.com
ISO 9001 Registered Company

PROPERTY OF ATI INDUSTRIAL AUTOMATION, INC. NOT TO BE REPRODUCED IN ANY MANNER EXCEPT ON ORDER OR WITH PRIOR WRITTEN AUTHORIZATION OF ATI.

DRAWN BY: Dan Norton 3/16/09	TITLE: Manual Coupler with Quick Action Screw Lock		
CHECKED BY: _	SCALE: 1:1.5	SIZE: B	REVISION: 03
WEIGHT LBS: 3.33	DRAWING NUMBER: 9230-20-2934		
ASSEMBLY REF:	PRODUCT RELEASE # 070724-1 DATE: SHEET 1 OF 1		