

Technische Daten

LPE 100

product name	unit	LPE 100-...-...-...-
Order example		LPE 100-S800-Y1000-Z100-M
max. load	[kg]	10
pillar length	[mm]	400, 600, 800
y-axis		
stroke	[mm]	500, 800, 1000, 1200, 1500
acceleration	[m/s ²]	5
speed	[m/s]	1
repeatability	[mm]	+/- 0,08
axis type		B 100D-ZSS
drive option		
drive type		BoschRexroth MSK050B
gear type		BoschRexroth GTE120
z-axis		
stroke	[mm]	100, 300, 500
acceleration	[m/s ²]	2
speed	[m/s]	0,25
repeatability	[mm]	+/- 0,03
axis type		B 60-SSS
option with drive		
drive type		BoschRexroth MSK040B
gear type		BoschRexroth GTE120