

technical data

LPP 50

product name	unit	LPP 050-...-...-...
order example		LPP 050-S400-Y1000-Z100
load	[kg]	5
pillar length	[mm]	400, 600
y-axis		
stroke	[mm]	300, 400, 500, 600, 700, 800, 900, 1000, 1100, 1200, 1300, 1400, 1500
Stroke adjustment per side	[mm]	50
repeatability	[mm]	+/- 0,01
axis Typ		PMP-S 25
z-axis till 100mm stroke		
stroke	[mm]	50, 75, 100
Stroke adjustment per side	[mm]	25
repeatability	[mm]	+/- 0,01
axis Typ		CLM 100
z-axis till 225mm stroke		
stroke	[mm]	125, 175, 225
Stroke adjustment per side	[mm]	25
repeatability	[mm]	+/- 0,01
axis typ		LM 100