



Hand in hand for tomorrow



Product data sheet

Programmable magnetic switches MMS 22-PI2

Programmable. Precise. Easy assembly.

Programmable magnetic switch MMS 22-PI2

A magnetic switch is used to monitor the status of automation components. They detect the approach of a magnet without contact and above a certain switching value, they put out a digital value. The switching value can be programmed.

Field of application

Used for monitoring gripping and rotary modules, as well as linear modules, and robot accessories. Magnetic switches from SCHUNK detect magnets without contact or wear, and are resistant to vibrations, dust and humidity. Magnetic switches are installed in slots, and thus do not produce any additional interfering contours. For connection with a digital input module (utilization categorie DC-12).

Advantages – Your benefits

Individual switching point – without interfering contours

The magnetic switch can be completely inserted, which means that no interfering contours arise due to overhanging sensor systems

Programmable within no time due to non-contact adjustment of the switching points and hysteresis

Adjustable hysteresis for precise position monitoring – even at very low strokes

Suitable for narrow installation spaces due to wired teaching with TeachTool plug

Version with LED display for control of the switching position directly at the sensor

Version with standard plug connector for fast and easy exchangeability of the extension cable

Very flexible cable in PUR version for a long service life

Installation into the sensor groove for space-saving, easy, and fast assembly on the product



Options and special information

High protection class: IP67 when plugged in, for use in clean or dusty environments or in case of contact with water. Operability in case of contact with other media (coolant, acids, bases, etc.) is often given, however cannot be guaranteed by SCHUNK.

Power supply: 10 – 30 V DC at < 10% residual ripple

Sources of interference: Sensors can be influenced by other magnetic fields in the immediate vicinity. Disturbing magnetic fields can be generated by motors, electric welders, permanent magnets or magnetized material (so-called soft magnets) such as hexagon socket wrenches, chips, etc.

Application example



① Actuator

② MMS 22-PI2 C-slot sensor

③ Cable-based teaching tool ST

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Plug teaching tool



Sensor cables



Y distributor



Sensor distributor

① For more information on these products can be found on the following product pages or at [schunk.com](https://www.schunk.com).

MMS 22-PI2

Programmable magnetic switches




Technical data

Description		MMS 22-PI2-S-M8-PNP	MMS 22-PI2-S-M8-NPN	MMSK 22-PI2-S-PNP	MMSK 22-PI2-S-NPN
ID		0301180	0301181	0301182	0301183
Operating principle					
Measuring principle		magnetic	magnetic	magnetic	magnetic
Switching function		Closer	Closer	Closer	Closer
Type of switching		PNP	NPN	PNP	NPN
Number of switching points		2	2	2	2
Teach function		yes	yes	yes	yes
General data					
typical switching time	[s]	0.001	0.001	0.001	0.001
Max. switching frequency	[Hz]	1000	1000	1000	1000
Min./max. ambient temperature	[°C]	-20/80	-20/80	-20/80	-20/80
LED display in sensor		yes	yes	yes	yes
Electrical operating data					
Type of voltage		DC	DC	DC	DC
Nominal voltage	[V]	24	24	24	24
Min./max. operating voltage	[V]	10/30	10/30	10/30	10/30
Voltage drop	[V]	2	2	2	2
Max. switching current	[mA]	25	25	25	25
Short circuit protection		yes	yes	yes	yes
Protected against polarity reversal		yes	yes	yes	yes
Mechanical operating data					
Housing material		PA	PA	PA	PA
Cable connector/cable end		M8, 4-pin Male Connector	M8, 4-pin Male Connector	open wire strands	open wire strands
Cable length L	[cm]	31	31	200	200
Cable diameter D	[mm]	2.55	2.55	2.55	2.55
Cable design (wire cross section/ number of wires)		4x 0,05mm ²	4x 0,05mm ²	4x 0,05mm ²	4x 0,05mm ²
Cable sheath material		PUR	PUR	PUR	PUR
Min. bending radius (dynamic)	[mm]	25.5	25.5	25.5	25.5
Min. bending radius (static)	[mm]	12.75	12.75	12.75	12.75
Weight	[kg]	0.01	0.01	0.04	0.04
Protection class IP (sensor, plugged)		67	67	67	67
Protection class		III	III	III	III
Drilling emulsion resistance *		yes	yes	yes	yes
Options and their characteristics					
Version with lateral cable outlet		MMS 22-PI2-S-M8-PNP-SA		MMSK 22-PI2-S-PNP-SA	
ID		0301186		0301188	
LED display in sensor		yes		yes	
Heavy duty version		MMS 22-PI2-S-M8-PNP-HD		MMSK 22-PI2-S-PNP-HD	
ID		0301130		0301132	
Housing material		stainless steel		stainless steel	
Drilling emulsion resistance *		yes		yes	


* *Tested cutting emulsions: r.rhenus TU 43P, Motorex Swisscool Magnum UX 550 and Oemeta 760 (1008339).

MMS(K) 22-PI2 main view




- 65 Cable diameter
- 70 Wrench size
- 72 Active sensor surface
- 75 Cable length
- 76 LED

MMS(K) 22-PI2-SA main view




- 65 Cable diameter
- 70 Wrench size
- 72 Active sensor surface
- 75 Cable length
- 76 LED

MMS(K) 22-PI2-HD main view




- 65 Cable diameter
- 70 Wrench size
- 72 Active sensor surface
- 75 Cable length
- 76 LED

Wiring diagram closer PNP




Circuit diagram of NPN closer



MMS 22-PI2

Programmable magnetic switches

Pug-in teaching tool ST




90 Pug-in teaching tool ST 91 Sensor MMS 22-PI...

In addition to the magnetic teach-in tool included in the scope of delivery, the MMS 22-PI sensors can be taught via the plug teach-in tool. The plug teach in tool is inserted into the wiring from sensor to PLC. This makes teaching in possible even in confined spaces on the sensor. The plug teach in tool differs according to the version of the sensor with regard to switching points (1/2) and switching type (PNP / NPN).

Description	ID	
Sensor Teaching Tool		
MT-MMS 22-PI	0301030	

- 1 The plug-in teaching tool is only required for teaching in and can be removed from the cabling again after. The sensor maintains its programming.


View M8 connector (4 pins)



14 Connector

This view shows the plug connector on the cable end of the sensor.

Voltage supply/signals connection cable



KA G... Connection cable with straight socket
 KA W... Connection cable with angular socket

⑥ Connection module side
 ⑮ Socket
 ⑨⑩ SAC connection cable with open wire strands


⑨① Connection plug component
 ⑨② Cable with straight female connector
 ⑨③ Cable with angled female connector

The connection cable is ideal for connecting the corresponding components to the controller or the power supply unit. The connection cable has an M8 socket on one side and an open wire strand on the other side for individual connections. The connection cables are suitable for use both in the cable track as well as in torsion applications.

Description	ID	L1 [m]	D1 [mm]	L2 [mm]	D2 [mm]	L3 [mm]	D3	Often combined
Connection cables								
KA GLN0804-LK-00500-A	0307767	5	5.3	35	10		M8	●
KA GLN0804-LK-01000-A	0307768	10	5.3	35	10		M8	
KA WLN0804-LK-00500-A	0307765	5	5.3	29	10	20	M8	
KA WLN0804-LK-01000-A	0307766	10	5.3	29	10	20	M8	

① Please observe the min. bending radius for cable track-compatible cables or the max. torsion angle for torsion-compatible cables. These are generally 10 times the cable diameter or +/- 180°/m.

Clip for connector/socket



⑨⑩ CLI plug bracket
 ⑨① IN proximity switch
 ⑨② Magnetic switch MMS

The CLI clip is used for fastening and strain relief for the plug connectors. For example for the sensor and cable extension connection.

Description	ID
Clip for connector/socket	
CLI-M8	0301463



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

info@de.schunk.com

schunk.com

Folgen Sie uns | *Follow us*

