


Magnetic proximity sensor Series E22

Type **MMS 22-A-10V-M12**

Ident.-No. **0315828**

Wiring Diagram



Identifying characteristics in accordance with EN 60947-5-7

Elektrische Daten		
Rated operating voltage range	U_B	15 - 30 VDC
Voltage output		0 - 10 V
Linearity errors		max. $\pm 10\%$ from the end value (10 V), U_B and temperature at a constant level (MPG + 32)
Temperature errors		max. $\pm 2\%$ U_B constant level
Repeat accuracy	R	$\leq 2\%$ from the end value (10 V), U_B and temperature at a constant level
No-load supply current	I_0	< 15 mA
Utilization category		DC 12
Residual ripple		$\leq 2\%$ V_{SS}
Analogue output		permanently short-circuit and overload protected
Min. load resistance		10 k Ω (24 V DC)
False polarity protection		yes
Electromagnetic compatibility (EMC)		
acc. to EN 60947-5-7		
Mechanical data		
Enclosure		GV-5H (PA), black
Ambient air temperature		+5 °C ... +55 °C
Type of protection		IP 67 acc. to IEC 529, EN 60529 (only in fully locked position with it's plugs)
Function indication		LED, yellow
Termination type		Cable, PUR-Outer jacket, grey, shielded; with male connector M12
Attachment		1 x setscrew M2 x 3, DIN 913
		1 x allen wrench
		1 x magnetic programming tool
		1 x installation and operating instructions
EU Conformity		
acc. to directive 2004 / 108 / EC		
Remarks		
Internal-Type		MEK-E22A10/H50-KL0,3S12
Internal-Number		6470081169

SCHUNK GmbH & Co. KG . Bahnhofstraße 106–134 . D-74348 Lauffen/N.
Tel. 07133/103-0 . Fax 07133/103-189 . E-Mail: greifer@schunk.de . Internet: www.schunk.de

Technical modifications and errors excepted.

The technical datasheet corresponds to the technical state as of 2015-10-19 and will not be removed in case of changes.