



Superior Clamping and Gripping







Examples of EGM applications



VERY SMALL ROUND WORKPIECES WITH EGM-B 30L-1X2 + SPECIAL PVL (POLE EXTENSIONS)




BRAKE DISCS OF DIFFERENT TYPES AND ON BOTH SIDES USING A MATRIX OF EGM-M 30Q-1FX



UNLOADING OF SQUARE AND ROUND BARS FROM A SAWING MACHINE WITH A EGM-B 70Q-1X4 COMBINED WITH A SPECIAL DOUBLE ANGLE PVL




GRIPPING OF VERY THIN CYLINDERS (THICKNESS 1,2 mm) WITH 4 SPECIAL SHAPED EGM-M 08L-1FX



This drawing and associated information remain the confidential property of Schunk Inter Inc. The contents of this drawing may not be released to a third party without the expressed written permission of Schunk Inter Inc.		Undimensioned edges = 0,3x45°		Untoleranced dim. DIN 2768m	
125	32	68	11	-6	6
30	-30	-120	-400	-1000	400
±0,1	±0,2	±0,3	±0,5	±0,8	±0,8
ISO-E		A3		Thread Tolerance DIN 13	
Name		Date		Repl. to	
Drawn		19/05/2016		Repl. from	
Checked				Scale	
Applied				Customer	
SCHUNK		AT-0015		Sheet 1 of 1	

GRIPPING OF 7 PIPES TOGETHER USING A SPECIAL LONG VERSION OF EGM-M 15L



Superior Clamping and Gripping



www.schunk.com