





SPECIFICATIONS	
CONTACT CARRIER MATERIAL	TPU
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	3.0 A
RATED VOLTAGE [V]	30 VAC/VDC
MIN. BENDING RADIUS:	12X CABLE DIAMETER
MAX. TORSION ANGLE:	+/- 180° PER METER
OUTER JACKET MATERIAL/COLOR	TPE/BLACK
CONDUCTOR INSULATION MATERIAL	POLYESTER ELASTOMER
NUMBER OF CONDUCTORS [AWG]	19X22 AWG
TEMPERATURE RANGE	-40°C TO +105°C (-40°F TO +221°F)
PROTECTION CLASS	MEETS IEC IP67
FURTHER INFORMATION	
UNIT OF MEASUREMENT:	MILLIMETER [INCH]

WRAP LABEL DETAIL

SCHUNK®
Schunk ID Number:
302171
Schunk Part Number:
KV-10-SWK-19F-0
Made in _____
Date Code _____