



EGS 25-N-N-special with Signal Distributor


Gripping and moving of small to medium-sized workpieces with flexible force and high speed in clean environments, such as assembly, testing, laboratory and pharmaceutical industry

Your advantages and benefits

- **Control via digital I/O** for easy commissioning and rapid integration into existing systems
- **Virtually no wear parts** for high machine availability and low operating costs
- **Low space requirement** thanks to the compact merging of rotary drive and gripper
- **Two stage adjustable gripping force** for simple adaptation to sensitive workpieces
- **Four stage adjustable rotational speed** for high flexibility in the cycle time
- **Very high maximum cycles per minute** for the highest level of productivity
- **Backlash-free, pre-loaded cross roller** guide for high-precision and virtually constant gripping over the entire permissible finger length
- **Standardized mounting bores** for numerous combinations with other components from the modular system
- **1 mm additional opening stroke** compared to the standard module
- **1-cable solution** between the distributor and the wiring point

Please contact us with your individual requirement.
You can reach the Team Mechatronics at:

Mechatronics Hotline +49-7133-103-2992
E-mail: mechatronics@de.schunk.com



72 Fit for centering sleeves

80 Depth of the centering sleeve hole in the counter part

Technical data

Ergänzend zu den technischen Daten der Basiseinheit

- Size 25
- Stroke per jaw 4mm



J. Lehmann

Jens Lehmann, deutsche Torwartlegende,
seit 2012 SCHUNK-Markenbotschafter
für sicheres, präzises Greifen und Halten.
schunk.com/Lehmann

SCHUNK GmbH & Co. KG
Spann- und Greiftechnik

Bahnhofstr. 106 - 134
D-74348 Lauffen/Neckar
Tel. +49-7133-103-0
Fax +49-7133-103-2399
info@de.schunk.com

schunk.com
[youtube.com/schunkhq](https://www.youtube.com/schunkhq)
twitter.com/schunk_hq
facebook.com/schunk.hq
schunk.com/lehmann

