




Superior Clamping and Gripping



Spannbacken


Chuck Jaws

Backenschnellwechselsystem | Jaw Quick-change System


Spezialbacken | Special Jaws

Spitzverzahnung 1/16" x 90°

- Max. Spannbereich durch Versetzen der Trägerbacke möglich
- Liefereinheit und Gewichtsangaben: 1 Satz = 3 Stück
- Wechselbacken aus C45
- Material: Stahl 16MnCr5, einsatzgehärtet



Schnellwechselbacke, komplett
Quick-change jaw, complete



Trägerbacke BWT
Supporting jaw BWT

Fine Serration 1/16" x 90°

- Max. clamping range is possible by offsetting the supporting jaws
- Delivery unit and indication of weight: 1 set = 3 pieces
- Changing jaw made of C45
- Material: steel 16MnCr5, case-hardened

Bezeichnung Description	Ident.-Nr. ID	N [mm]	B [mm]	H [mm]	L ₁ [mm]	b [mm]	Schrauben Screws	m/Satz m/set [kg]
BWT 160	0105200	17	35	50	78	22	M12	1.4
BWT 200	0105201	17	40	60	85	28	M12	1.9
BWT 250	0105202	21	50	65	98	28	M16	2.6




Spanneinsätze, Ausdrehringe und Backen-Ausdrehvorrichtung




Clamping inserts, jaw turning rings and jaw turning fixture

Spitzverzahnung 1,5 mm x 60°

- Max. Spannbereich durch Versetzen der Trägerbacke möglich
- Liefereinheit und Gewichtsangaben: 1 Satz = 3 Stück
- Wechselbacken aus C45
- Material: Stahl 16MnCr5, einsatzgehärtet



Schnellwechselbacke, komplett
Quick-change jaw, complete



Trägerbacke BWT
Supporting jaw BWT

Fine Serration 1.5 mm x 60°

- Max. clamping range is possible by offsetting the supporting jaws
- Delivery unit and indication of weight: 1 set = 3 pieces
- Changing jaw made of C45
- Material: steel 16MnCr5, case-hardened

Bezeichnung Description	Ident.-Nr. ID	N [mm]	B [mm]	H [mm]	L ₁ [mm]	b [mm]	Schrauben Screws	m/Satz m/set
BWTJ-K-210-14	0105210	14	40	60	85	25	M12	1.9
BWTJ-K-250-16	0105211	16	40	60	85	30	M12	1.9
BWTJ-K-305-18	0105212	18	50	70	98	30	M14	3.8
BWTJ-K-305-21	0105213	21	50	70	98	30	M16	3.8

 Spanneinsätze, Ausdrehringe und Backen-Ausdrehvorrichtung


 Clamping inserts, jaw turning rings and jaw turning fixture

Backenschnellwechselsystem | Jaw Quick-change System

Spezialbacken | Special Jaws

Wechselbacke BWW

- Trägerbacken aus hochfestem Aluminium
- Spanneinsätze aus glasfaserverstärktem Kunststoff
- Hoher Reibwert ca. 0,3–0,4
- Schonende Spannung



Schnellwechselbacke, komplett
Quick-change jaw, complete



Wechselbacke BWW
Soft insert BWW

Soft Insert BWW

- Supporting jaws made of high-strength aluminum
- Clamping inserts of glass fiber reinforced plastic
- High friction coefficient of approx. 0.3–0.4
- Gentle clamping

Bezeichnung Description	Ident.-Nr. ID	B [mm]	H ₁ [mm]	H _{1max} [mm]	L ₁ [mm]	L ₂ [mm]	L _{2max}	m/Satz m/set [kg]
BWW 160	0105305	35	25.7	17	89	65	6	1.3
BWW 200	0105306	40	30.7	22	105	75	8	2.1
BWW 250	0105306	50	35.7	27	125	2905	8	3.6



Weiche Auflagebolzen



Soft workpiece stops