




SCHUNK Spannbacken für ROTA THW3 260-81


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 250	0159101	20	12	26		37	104		40	M12	1.8
	GBKL 250	0159121	20	12	26		37	125		40	M12	2.4
	GBK-V 250	0159151	20	12	26		37	104		40	M12	1.8
	STN 250-5	0160600	17		26	40	48	86	10	22	M12	2.6
	STN 250-6	0160601	21		26	45	52	110	13	28	M16	4


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Stahl	1.9


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 251	0162105	26	65	36	107.4	10	Stahl	2.8


Krallenbacken für Außenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Stahl	1.9
	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Stahl	2.2
	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Stahl	1.4
	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Stahl	1.9

Krallenbacken für Innenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Stahl	2.8
	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2
	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2

Krallenbacken für Stangenspannung


	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Stahl	1.2





Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für ROTA THW3 260-81


Pendelbacken

	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	PNK-G 250-2	0190601	86	40	1.8
	PNK-G 250-6	0190605	86	40	2.2
	PNK-G 250-8	0190607	86	40	2.4
	PNK-G 250-10	0190609	86	40	2.5



QUENTES Kunststoffbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	TRQK 250-2	0150012	12	20	40	57	72	40	M12	0.7
	TRQK 250-1	0150011	12	20	38	53	98	40	M12	0.8

Universalaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	m/Satz [kg]
	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6
	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6

Weiche Aufsatzbacken




	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Stahl	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Stahl	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Stahl	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Stahl	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Stahl	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Stahl	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Stahl	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Stahl	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Stahl	20.9
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminium	2.1





Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für ROTA THW3 260-81

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 250	0164101	26		84	55		99	Stahl	4.8
	UVB-H 250	0164117	26		115	86		99	Stahl	6.6
	UVB-B 250	0164114	26	46	84	52		99	Stahl	7.2
	UVB-HS 250	0164120	26		115	86	48	99	Stahl	5.25

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Stahl	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Stahl	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminium	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminium	6.4



Technische Beratung und Verkauf: Tel. +49-7133-103-2750