




### Backenrohlinge

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Min. Abstand<br>a<br>[mm] | Min. Abstand<br>b<br>[mm] | Schrauben | Werkstoff | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|---------------------------|---------------------------|-----------|-----------|-----------------|
|  | SBM 41      | 0112112    | 21        | 50        | 60        | 90        | 15                        | 28                        | M16       | Stahl     | 2.1             |
|                                                                                   | SBM 42      | 0112113    | 21        | 50        | 60        | 105       | 15                        | 28                        | M16       | Stahl     | 2.4             |
|                                                                                   | SBM 4210    | 0112115    | 21        | 50        | 100       | 120       | 15                        | 28                        | M16       | Stahl     | 5               |
|                                                                                   | SBM 4212    | 0112116    | 21        | 50        | 120       | 120       | 15                        | 28                        | M16       | Stahl     | 5.6             |
|                                                                                   | SBM 4215    | 0112117    | 21        | 50        | 150       | 120       | 15                        | 28                        | M16       | Stahl     | 7               |
|                                                                                   | SBM 428     | 0112114    | 21        | 50        | 80        | 120       | 15                        | 28                        | M16       | Stahl     | 3.7             |
|                                                                                   | SBM 4281    | 0112137    | 21        | 50        | 80        | 150       | 15                        | 28                        | M16       | Stahl     | 4.6             |
|                                                                                   | SBM 43      | 0112118    | 21        | 60        | 60        | 90        | 15                        | 28                        | M16       | Stahl     | 2.4             |
|                                                                                   | SBM 44      | 0112119    | 21        | 60        | 60        | 105       | 15                        | 28                        | M16       | Stahl     | 2.9             |
|                                                                                   | SBM 45      | 0112120    | 21        | 60        | 80        | 90        | 15                        | 28                        | M16       | Stahl     | 3.2             |
|                                                                                   | SBM 46      | 0112121    | 21        | 60        | 80        | 105       | 15                        | 28                        | M16       | Stahl     | 3.8             |
|                                                                                   | SBM 47      | 0112122    | 21        | 60        | 80        | 120       | 15                        | 28                        | M16       | Stahl     | 4.4             |
|                                                                                   | SBM 48      | 0112123    | 21        | 80        | 60        | 90        | 15                        | 28                        | M16       | Stahl     | 3.2             |
|                                                                                   | SBM 498     | 0112125    | 21        | 80        | 80        | 120       | 15                        | 28                        | M16       | Stahl     | 5.8             |


### Harte Stufenaufsatzbacken

|                                                                                    | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 250     | 0121105    | 21        | 50        | 58        | 103.5     | 14        | 34        | 25        | 25        | M16       | Stahl     | 3.5            |
|                                                                                    | SHB 315     | 0121111    | 21        | 50        | 58        | 128       | 14        | 46        | 30        | 30        | M16       | Stahl     | 4.6            |

### Krallenbacken für Außenspannung


|                                                                                     | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 62 - 106           | 278                   | SZA 25-37   | 0138180    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.3            |
|                                                                                     | 101 - 146          | 279                   | SZA 25-38   | 0138181    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 2.9            |
|                                                                                     | 151 - 195          | 282                   | SZA 25-39   | 0138182    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 2.7            |
|                                                                                     | 198 - 242          | 317                   | SZA 25-40   | 0138183    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.2            |
|                                                                                     | 46 - 83            | 288                   | SZA 31-10   | 0138184    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.4            |
|                                                                                     | 97 - 141           | 290                   | SZA 31-11   | 0138185    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.4            |
|                                                                                     | 162 - 207          | 288                   | SZA 31-12   | 0138186    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.2            |
|                                                                                     | 225 - 270          | 348                   | SZA 31-13   | 0138187    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 4.5            |

### Krallenbacken für Innenspannung


|                                                                                     | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G  | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|----|-----------|-----------|-----------|----------------|
|  | 91 - 134           | 285                   | SZI 25-34   | 0123183    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.5            |
|                                                                                     | 132 - 176          | 288                   | SZI 25-35   | 0123184    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.2            |
|                                                                                     | 177 - 221          | 287                   | SZI 25-36   | 0123185    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3              |
|                                                                                     | 80 - 105           | 295                   | SZI 31-11   | 0123186    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 4.1            |
|                                                                                     | 127 - 158          | 287                   | SZI 31-12   | 0123187    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 4.2            |
|                                                                                     | 187 - 232          | 287                   | SZI 31-13   | 0123188    | 21        | 50        | 58        | 25        | M8 | 28        | M16       | Stahl     | 3.9            |




### Krallenbacken für Stangenspannung

|                                                                                   | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|--------------------|-----------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | 31 - 75            | 280                   | SZA-ST 25-2 | 0175103    | 21        | 45        | 50        | 40        | 28        | M16       | Stahl     | 2.7            |
|                                                                                   | 20 - 45            | 287                   | SZA-ST 31-1 | 0175104    | 21        | 45        | 50        | 40        | 28        | M16       | Stahl     | 3.3            |




### Pendelbacken

|                                                                                   | Spannbereich<br>ØD | Schwingkreis<br>SDmax | Bezeichnung    | Ident.-Nr. | H<br>[mm] | T<br>[mm] | m/Stück<br>[kg] |
|-----------------------------------------------------------------------------------|--------------------|-----------------------|----------------|------------|-----------|-----------|-----------------|
|  | 85 - 115           | 277                   | PNS-Z 250-21-2 | 0190106    | 64        | 35        | 2               |
|                                                                                   | 89 - 113           | 277                   | PNS-Z 250-21-3 | 0190107    | 64        | 35        | 2.1             |
|                                                                                   | 141 - 171          | 295                   | PNS-Z 250-21-4 | 0190108    | 64        | 35        | 2.3             |
|                                                                                   | 150 - 180          | 295                   | PNS-Z 250-21-5 | 0190109    | 64        | 35        | 2.3             |
|                                                                                   | 69 - 99            | 277                   | PNS-Z 315-1    | 0190110    | 64        | 35        | 2               |
|                                                                                   | 97 - 113           | 277                   | PNS-Z 315-2    | 0190111    | 64        | 35        | 2.3             |
|                                                                                   | 146 - 176          | 295                   | PNS-Z 315-3    | 0190112    | 64        | 35        | 2.5             |
|                                                                                   | 163 - 186          | 297                   | PNS-Z 315-4    | 0190113    | 64        | 35        | 2.7             |

### Verzahnte Stangen



|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | Werkstoff | m/Stück<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------------|
|  | SBM-ST 210  | 0112180    | 21        | 50        | 60        | 420       | Stahl     | 9.4             |
|                                                                                     | SBM-ST 211  | 0112181    | 21        | 50        | 80        | 420       | Stahl     | 12.7            |
|                                                                                     | SBM-ST 212  | 0112182    | 21        | 50        | 120       | 420       | Stahl     | 19.3            |
|                                                                                     | SBM-ST 213  | 0112183    | 21        | 80        | 80        | 420       | Stahl     | 20.4            |
|  | SBM-STA 210 | 0112184    | 21        | 50        | 80        | 420       | Aluminium | 4.6             |

### Weiche Aufsatzbacken


|                                                                                     | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a1<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|-----------|----------------|
|  | SWBL 250-21 | 0120155    | 21        | 50        | 50        | 120       | 4          | 20        | 28        | M16       | Stahl     | 5.6            |
|                                                                                     | SWBL 315    | 0120156    | 21        | 50        | 50        | 140       | 4          | 30        | 28        | M16       | Stahl     | 6.5            |
|  | 2 SWK 200   | 0126102    | 21        | 80        | 80        | 95        |            | 22        | 28        | M16       | Stahl     | 8.2            |
|                                                                                     | CWB 251     | 0100012    | 21        | 50        | 60        | 95        |            | 15        | 28        | M16       | Stahl     | 5.2            |
|                                                                                     | SWB 250     | 0120105    | 21        | 50        | 80        | 120       |            | 30        | 28        | M16       | Stahl     | 9.4            |
|                                                                                     | SWB-FR 315  | 0120406    | 21        | 50        | 60        | 105       |            | 15        | 25        | M16       | Stahl     | 6              |
|  | SWB-AL 250  | 0168102    | 21        | 50        | 80        | 120       |            | 30        | 28        | M16       | Aluminium | 3              |



### Weiche Segmentbacken

|                                                                                   | Bezeichnung   | Ident.-Nr. | N<br>[mm] | B<br>[mm] | B1<br>[mm] | Ø D<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|---------------|------------|-----------|-----------|------------|-------------|-----------|------------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SWB-SM 250-21 | 0169103    | 21        | 180       | 104        | 250         | 70        | 55         | 80        | 30        | 28        | M16       | Stahl     | 14             |
|                                                                                   | SWB-SM 251    | 0169107    | 21        | 180       | 104        | 250         | 100       | 85         | 80        | 30        | 28        | M16       | Stahl     | 21.7           |
|                                                                                   | SWB-SM 315    | 0169104    | 21        | 240       | 120        | 320         | 70        | 55         | 110       | 60        | 28        | M16       | Stahl     | 26.6           |
|  | SWB-SA 250-21 | 0170103    | 21        | 180       | 70         | 250         | 78        | 63         | 87.5      | 40        | 28        | M16       | Aluminium | 7.3            |
|                                                                                   | SWB-SA 251    | 0170107    | 21        | 180       | 70         | 250         | 100       | 85         | 87.5      | 40        | 28        | M16       | Aluminium | 8.3            |
|                                                                                   | SWB-SA 315    | 0170104    | 21        | 240       | 80         | 320         | 78        | 63         | 117       | 70        | 28        | M16       | Aluminium | 12             |

### Nutenstein

|                                                                                    | Bezeichnung | Ident.-Nr. | S<br>[mm] | H<br>[mm] | H1<br>[mm] | b<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdrehmo-<br>ment<br>[Nm] |
|------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----------|-----|---------------|--------------------------------------------|
|   | NKS 3       | 0143107    | 21        | 26.5      | 10         |           | M16 | M16 x 35      | 150                                        |
|  | NKA 3       | 0145105    | 21        | 26.5      | 10         | 28        | M16 | M16 x 35      | 150                                        |

