



Hand in hand for tomorrow



Product data sheet

Linear module KLM 50

Modular. Robust. Reliable.

Linear module KLM

Linear module with pneumatic drive and ball bushing guide

Field of application

For use in clean and slightly polluted environments. Simple economic linear movements or, in combination, as multi-axis positioning systems for assembly and handling Technology.



Advantages – Your benefits

Double bearing of the guide shafts in the ball bushing for high load bearing capacity and repeat accuracy < 0.015 mm

Shock absorbers and proximity switches integrated in the projecting surfaces for vibration-free movements and end position monitoring

Strongly dimensioned guide shafts for high rigidity

High basic load ratings in all load directions

Standardized mounting bores for numerous combinations with other components from the modular system

Several intermediate positions possible for maximum flexibility in applications

Rod lock by means of clamping cartridge for safety in case of emergency stops



Sizes
Quantity: 4



Weight
0.5 .. 13.2 kg



Driving force
67 .. 753 N




Stroke
13 .. 300 mm



Repeat accuracy
0.02 .. 0.03 mm

Functional description

The linear module is driven via a double-acting pneumatic cylinder which is integrated in the base body, and guided by two opposing guide rods.



- ① **Ball bushing guide**
scope-free at a low friction
- ② **Drive**
Powerful piston rod cylinders
- ③ **Mounting pattern**
Completely integrated in the module system
- ④ **Damping adjustment**
Adjustment of the damping characteristics
- ⑤ **End position adjustability**
Convenient adjustment using the shock absorber threads
- ⑥ **Sensor system**
with sensor driver for convenient adjustment

General notes about the series

Housing material: Aluminum alloy, anodized

Guidance: Ball bushing guide

Actuation: pneumatic, with filtered compressed air as per ISO 8573-1:2010 [7:4:4].

Scope of delivery: Shock absorber and driver for proximity switch

Warranty: 24 months

Service life characteristics: on request


Repeat accuracy: is defined as a distribution of the end positions for 100 consecutive cycles.

Travel times: are pure movement times of the slide or the base body. Valve switching times, hose filling times, or PLC reaction times are not a part of this and are to be considered when cycle times are calculated.

Stroke: is the maximum nominal stroke of the unit. It can be shortened on both sides by the shock absorbers.

Layout or control calculation: For configuration or control calculation of the units, we recommend to use our Toolbox software, which is available online. A control calculation for the selected unit must be carried out to prevent overloading.

Ambient conditions: The modules are mainly designed for the use in clean ambient conditions. Please note that the life time of the modules can shorten if they are used in harsh ambient conditions, and that SCHUNK cannot assume liability in such cases. Please contact us for assistance.



Application example

Sorting unit for small components which require an especially long gripper stroke due to their variation in size.


- ① 2-finger parallel gripper KGG with workpiece-specific fingers
- ② Linear module KLM for vertical movement
- ③ Linear module KLM for horizontal movement

SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



Vane swivel unit




Rotary indexing table



Gripper for small components



Universal gripper



Rod lock



Intermediate stop cylinder



Pillar assembly system



Rotary gripper module



Pressure maintenance valve



Inductive proximity switch


① For more information on these products can be found on the following product pages or at [schunk.com](https://www.schunk.com).

Options and special information

Version rod lock: prevents the structure from falling in the event of a sudden loss of energy. This module can be combined as standard with many elements from the modular system. We can assist you with questions.

Food-grade lubrication: The product contains food-compliant lubricants as standard. The requirements of standard EN 1672-2:2020 are not fully met. The relevant NSF certificates are available at <https://info.nsf.org/USDA/Listings.asp> using the lubricant information in the operating manual. Components such as rolling bearings, linear guides, or shock absorbers are not provided with food-compliant lubricants.

Dimensions and maximum loads




- ① The indicated forces and moments are maximum values for single load. If more than one force and/or torque occurs simultaneously, the case of application can be calculated by using the Toolbox. The force F_y can only be calculated by using the Toolbox.

Technical data

Description		KLM 50-H013	KLM 50-H025	KLM 50-H038	KLM 50-H050	KLM 50-H063	KLM 50-H075
ID		0314013	0314014	0314015	0314016	0314017	0314018
Stroke	[mm]	13	25	38	50	63	75
extend force	[N]	120	120	120	120	120	120
retracted force	[N]	103	103	103	103	103	103
Repeat accuracy	[mm]	0.02	0.02	0.02	0.02	0.02	0.02
Piston diameter	[mm]	16	16	16	16	16	16
Bar diameter	[mm]	6	6	6	6	6	6
Min./nom./max. operating pressure	[bar]	3/6/8	3/6/8	3/6/8	3/6/8	3/6/8	3/6/8
Cylinder volume/10 mm per double stroke	[cm ³]	2	2	2	2	2	2
Overall length	[mm]	150	150	200	200	250	250
IP protection class		40	40	40	40	40	40
Min./max. ambient temperature	[°C]	5/60	5/60	5/60	5/60	5/60	5/60
Cleanroom class ISO 14644-1:1999		6	6	6	6	6	6
Weight	[kg]	1.3	1.3	1.5	1.5	1.7	1.7
Drive concept		Piston rod cylinders	Piston rod cylinders	Piston rod cylinders	Piston rod cylinders	Piston rod cylinders	Piston rod cylinders
Dimensions X x Y x Z	[mm]	150 x 65 x 45	150 x 65 x 45	200 x 65 x 45	200 x 65 x 45	250 x 65 x 45	250 x 65 x 45
Clearance N (for moment load)	[mm]	32.5	32.5	32.5	32.5	32.5	32.5
Moments Mx max./My max./Mz max.	[Nm]	11.4/23/23	11.4/23/23	9.2/30.5/30.5	9.2/30.5/30.5	6.5/29/29	6.5/29/29
Forces Fz max.	[N]	569	569	461	461	324	324
Options and their characteristics							
Dustproof version		KLM 50-H013-SD	KLM 50-H025-SD	KLM 50-H038-SD	KLM 50-H050-SD	KLM 50-H063-SD	KLM 50-H075-SD
ID		0314640	0314641	0314642	0314643	0314644	0314645
IP protection class		50	50	50	50	50	50
Rod lock version			KLM 50-H025-ASP	KLM 50-H038-ASP	KLM 50-H050-ASP	KLM 50-H063-ASP	KLM 50-H075-ASP
ID			0314414	0314415	0314416	0314417	0314418
Stroke loss of nominal stroke (on the rod side)	[mm]		10	10	10	10	10
Weight	[kg]		1.34	1.54	1.54	1.74	1.74
Static holding force	[N]		180	180	180	180	180
Max. axial play of the clamping	[mm]		0.2	0.2	0.2	0.2	0.2
Min. release pressure	[bar]		3	3	3	3	3

Description		KLM 50-H088	KLM 50-H100	KLM 50-H113	KLM 50-H125
ID		0314019	0314020	0314021	0314022
Stroke	[mm]	88	100	113	125
extend force	[N]	120	120	120	120
retracted force	[N]	103	103	103	103
Repeat accuracy	[mm]	0.02	0.02	0.02	0.02
Piston diameter	[mm]	16	16	16	16
Bar diameter	[mm]	6	6	6	6
Min./nom./max. operating pressure	[bar]	3/6/8	3/6/8	3/6/8	3/6/8
Cylinder volume/10 mm per double stroke	[cm ³]	2	2	2	2
Overall length	[mm]	300	300	350	350
IP protection class		40	40	40	40
Min./max. ambient temperature	[°C]	5/60	5/60	5/60	5/60
Cleanroom class ISO 14644-1:1999		6	6	6	6
Weight	[kg]	1.9	1.9	2.1	2.1
Drive concept		Piston rod cylinders	Piston rod cylinders	Piston rod cylinders	Piston rod cylinders
Dimensions X x Y x Z	[mm]	300 x 65 x 45	300 x 65 x 45	350 x 65 x 45	350 x 65 x 45
Clearance N (for moment load)	[mm]	32.5	32.5	32.5	32.5
Moments Mx max./My max./Mz max.	[Nm]	4.5/26.5/26.5	4.5/26.5/26.5	3.2/23.5/23.5	3.2/23.5/23.5
ForcesFz max.	[N]	224	224	164	164
Options and their characteristics					
Dustproof version		KLM 50-H088-SD	KLM 50-H100-SD	KLM 50-H113-SD	KLM 50-H125-SD
ID		0314646	0314647	0314648	0314649
IP protection class		50	50	50	50
Rod lock version		KLM 50-H088-ASP	KLM 50-H100-ASP	KLM 50-H113-ASP	KLM 50-H125-ASP
ID		0314419	0314420	0314421	0314422
Stroke loss of nominal stroke (on the rod side)	[mm]	10	10	10	10
Weight	[kg]	1.94	1.94	2.14	2.14
Static holding force	[N]	180	180	180	180
Max. axial play of the clamping	[mm]	0.2	0.2	0.2	0.2
Min. release pressure	[bar]	3	3	3	3

Main view




The linear module can be fastened either to the base body or the face plates. The structure can also optionally be fastened to either the face plates or the base body. This view shows the mounting of the module to the base body and the mounting of the structure to the face plates.

- A Main connection – linear unit extended
- B Main connection – linear unit retracted
- ① Connection linear unit
- ② Attachment connection
- ③④ On both sides

- ③⑤ Back side
- ⑦③ Fit for centering pins
- ⑨⑩ Through-holes in the face plate and thread in the base body (only single sided)
- ⑨① Inductive proximity switch
- ⑨② Fit for centering strip LMZL


Description	ID	A	B	Quantity B	C	Quantity C	D	E	G
		[mm]	[mm]		[mm]		[mm]	[mm]	[mm]
KLM 50-H013	0314013	150	25	1	25	1	21	83	46
KLM 50-H025	0314014	150	25	1	25	1	21	83	46
KLM 50-H038	0314015	200	25	2	25	2	21	108	71
KLM 50-H050	0314016	200	25	2	25	2	21	108	71
KLM 50-H063	0314017	250	25	3	25	3	21	133	96
KLM 50-H075	0314018	250	25	3	25	3	21	133	96
KLM 50-H088	0314019	300	25	4	25	4	21	158	121
KLM 50-H100	0314020	300	25	4	25	4	21	158	121
KLM 50-H113	0314021	350	25	5	25	5	21	183	146
KLM 50-H125	0314022	350	25	5	25	5	21	183	146

Dustproof version



The "dustproof" option increases the degree of protection against penetrating substances.


Fine adjustment



- ⑨ Nominal stroke
- ⑤① Stroke adjustment range
- ⑤① Damping stroke adjustment range

Shock absorbers can be mounted either on the base body or on the face plates. This illustration shows the mounting on the face plates and the possibility of stroke fine adjustment.


Fine adjustment



- ⑨ Nominal stroke
- ⑤① Stroke adjustment range
- ⑤① Damping stroke adjustment range

Shock absorbers can be mounted either on the base body or on the face plates. This illustration shows the mounting on the base body and the possibility of stroke fine adjustment.

Rod lock




- ③② Pneumatic connection for holding brake

The rod lock prevents weights from falling in the event of energy loss, such as emergency stop situations. The rod lock can also be retrofitted, but this will reduce the nominal stroke.

Description	D	E	G
	[mm]	[mm]	[mm]
KLM 50-H025-ASP	21	93	36
KLM 50-H038-ASP	21	118	61
KLM 50-H050-ASP	21	118	61
KLM 50-H063-ASP	21	143	86
KLM 50-H075-ASP	21	143	86
KLM 50-H088-ASP	21	168	111
KLM 50-H100-ASP	21	168	111
KLM 50-H113-ASP	21	193	136
KLM 50-H125-ASP	21	193	136

Attachment to a pillar assembly system




- ④ Linear unit
- ⑨① Pillars, hard-chromium plated, ground
- ⑨② Double socket SOD
- ⑨② Double socket SOD

This unit can be attached to the pillar assembly system as standard. See the Kombibox software, which can be found online, for the right arrangement for your application.

Description	ID	pillar diameter	Material
		[mm]	
Pillar assembly system mounting plate			
APDH 85	0313414	55	Aluminum
APDV 35	0313896	35	Aluminum
APDV 85	0313416	55	Aluminum
APEH 35	0313893	35	Aluminum
APEH 85	0313413	55	Aluminum
APEV 35	0313895	35	Aluminum
APEV 85	0313415	55	Aluminum


Modular Assembly Automation



- ④ Grippers
- ⑨① ASG adapter plate
- ⑨② Linear module CLM/KLM/LM/ELP/ELM/ELS/HLM
- ⑨② Linear module CLM/KLM/LM/ELP/ELM/ELS/HLM

Grippers and linear modules can be combined with standard adapter plates from the modular assembly system. For more information see our main catalog "Modular Assembly Automation".

Intermediate stop, ZZA on the piston side



①⑨ Air connection

⑤② Intermediate stroke


⑨① Overall length "A," the variant without intermediate stroke (see measurement chart of stroke variants)

The intermediate position is measured from the respective end position. The intermediate position can be approached from both sides and can proceed in the original stroke direction. The holding force is the piston force of the intermediate stop less the piston force of the linear module.

Description	Holding force	With with 0mm stroke	Weight per mm stroke
	[N]	[kg]	[kg]
Intermediate stop			
ZZA 55	175	0.35	0.003

① Sample order KLM 50-H100-ZZA055-H30

Intermediate stop, ZZA on the piston rod side



①⑨ Air connection

⑤② Intermediate stroke


⑨① Overall length "A," the variant without intermediate stroke (see measurement chart of stroke variants)

The intermediate position is measured from the respective end position. The intermediate position can be approached from both sides and can proceed in the original stroke direction. The holding force is the piston force of the intermediate stop less the piston force of the linear module.

Description	Holding force	With with 0mm stroke	Weight per mm stroke
	[N]	[kg]	[kg]
Intermediate stop			
ZZA 56	175	0.35	0.003

① Sample order KLM 50-H100-ZZA056-H30

Design – variant 1




⑨① Nominal stroke

⑨② Intermediate stroke

The corresponding intermediate stroke (ZH) is calculated by subtracting the intermediate stop cylinder stroke from the nominal stroke of the module. The intermediate stroke adjustment is ± 3 mm.

Design – variant 2




⑨① Nominal stroke

⑨② Intermediate stroke

The corresponding intermediate stroke (ZH) is calculated by subtracting the intermediate stop cylinder stroke from the nominal stroke of the module. The intermediate stroke adjustment is ± 3 mm.

Inductive proximity switches



Directly mounted end position monitoring.

Description	ID	Often combined
Inductive proximity switch		
IN 40-S-M12	0301574	
IN 40-S-M8	0301474	●
INK 40-S	0301555	
Inductive proximity switch with lateral cable outlet		
IN 40-S-M12-SA	0301577	
IN 40-S-M8-SA	0301473	●
INK 40-S-SA	0301565	
Connection cables		
KA BG08-L 3P-0300-PNP	0301622	●
KA BG08-L 3P-0500-PNP	0301623	
KA BG12-L 3P-0500-PNP	30016369	
KA BW08-L 3P-0300-PNP	0301594	
KA BW08-L 3P-0500-PNP	0301502	
KA BW12-L 3P-0300-PNP	0301503	
KA BW12-L 3P-0500-PNP	0301507	
Clip for connector/socket		
CLI-M12	0301464	
CLI-M8	0301463	
Cable extension		
KV BG12-SG12 3P-0030-PNP	0301999	
KV BG12-SG12 3P-0060-PNP	0301998	
KV BW08-SG08 3P-0030-PNP	0301495	
KV BW08-SG08 3P-0100-PNP	0301496	
KV BW08-SG08 3P-0200-PNP	0301497	●
KV BW12-SG12 3P-0030-PNP	0301595	
KV BW12-SG12 3P-0100-PNP	0301596	
KV BW12-SG12 3P-0200-PNP	0301597	
Sensor distributor		
V2-M12	0301776	●
V2-M8	0301775	●
V4-M8	0301746	
V8-M8	0301751	

① Two sensors are required per unit for monitoring two positions. On option, extension cables and sensor distributors are available. Additional product variants of the sensor, and further information and technical data can be found in the catalog chapter sensor system.



SCHUNK SE & Co. KG

Spanntechnik

Greiftechnik

Automatisierungstechnik

Bahnhofstr. 106 - 134

D-74348 Lauffen/Neckar

Tel. +49-7133-103-0

Fax +49-7133-103-2399

info@de.schunk.com

schunk.com

Folgen Sie uns | *Follow us*

