





Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 250	0159101	20	12	26		37	104		40	M12	1.8
	GBKL 250	0159121	20	12	26		37	125		40	M12	2.4
	GBK-V 250	0159151	20	12	26		37	104		40	M12	1.8
	STN 250-5	0160600	17		26	40	48	86	10	22	M12	2.6
	STN 250-6	0160601	21		26	45	52	110	13	28	M16	4


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Stahl	1.9


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 251	0162105	26	65	36	107.4	10	Stahl	2.8


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	145 - 221	316	I	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Stahl	1.9
	178 - 255	330	I	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Stahl	2.2
	31 - 101	313	II	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Stahl	1.4
	83 - 158	313	II	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Stahl	1.9

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	69 - 140	312	I	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Stahl	2.8
	182 - 259	313	I	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2
	120 - 196	312	II	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2


Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	17 - 84	313	II	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Stahl	1.2

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	57 - 91	274	PNK-G 250-2	0190601	86	40	1.8
	85 - 117	299	PNK-G 250-6	0190605	86	40	2.2
	120 - 180	305	PNK-G 250-8	0190607	86	40	2.4
	129 - 192	308	PNK-G 250-10	0190609	86	40	2.5

QUENTES Kunststoffbacken

	Spannbereich ØD	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	55 - 124	TRQK 250-2	0150012	12	20	40	57	72	40	M12	0.7
	20 - 98	TRQK 250-1	0150011	12	20	38	53	98	40	M12	0.8




Universalaufsatzbacken

	Spannbereich ØD	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	m/Satz [kg]
	163 - 207	I	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6
	99 - 143	II	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6



Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Stahl	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Stahl	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Stahl	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Stahl	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Stahl	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Stahl	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Stahl	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Stahl	8.5
SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Stahl	20.9	
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminium	2.1

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 250	0164101	26		84	55		99	Stahl	4.8
	UVB-H 250	0164117	26		115	86		99	Stahl	6.6
	UVB-B 250	0164114	26	46	84	52		99	Stahl	7.2
	UVB-HS 250	0164120	26		115	86	48	99	Stahl	5.25

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Stahl	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Stahl	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminium	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminium	6.4

