




SCHUNK Spannbacken für ROTA THW3 315-104


Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	GBK 315	0159102	20	12	32		43	115		40	M12	3
	GBKL 315	0159122	20	12	32		43	137		40	M12	3.5
	GBK-V 315	0159152	20	12	32		43	115		40	M12	3
	STNJ 315-5	0160652	18		32	50	54	120	15	30	M14	4.9
	STNJ 315-6	0160665	21		32	50	58	125	17.5	30	M16	5.5
	STN 315-6	0160603	21		32	45	56	110	13	28	M16	4.5


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Stahl	1.9


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	GST 315	0162102	32	66	32	116.3	10	Stahl	3.5


Krallenbacken für Außenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Stahl	2.2
	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Stahl	1.4
	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Stahl	2.2

Krallenbacken für Innenspannung

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Stahl	2.8
	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2
	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2

Krallenbacken für Stangenspannung


	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Stahl	1.2





Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für ROTA THW3 315-104


Pendelbacken

	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	PNK-G 315-2	0190611	93	40	2.6
	PNK-G 315-4	0190613	93	40	2.8
	PNK-G 315-6	0190615	93	40	3.1
	PNK-G 315-8	0190617	93	40	4


QUENTES Kunststoffbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	TRQK 250-2	0150012	12	20	40	57	72	40	M12	0.7
	TRQK 250-1	0150011	12	20	38	53	98	40	M12	0.8

Universalaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	m/Satz [kg]
	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6
	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6

Weiche Aufsatzbacken




	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Stahl	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Stahl	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Stahl	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Stahl	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Stahl	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Stahl	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Stahl	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Stahl	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Stahl	20.9



Technische Beratung und Verkauf: Tel. +49-7133-103-2750

SCHUNK Spannbacken für ROTA THW3 315-104

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	UVB 315	0164102	32		90	56		121	Stahl	7.6
	UVB-H 315	0164118	32		135	101		121	Stahl	11.3
	UVB-B 315	0164115	32	46	90	52		121	Stahl	9.6
	UVB-HS 315	0164121	32		135	101	52	121	Stahl	9



Technische Beratung und Verkauf: Tel. +49-7133-103-2750