





Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	SFG 200	0157101	20	10	22		32	90	40	M8x1	1.2
	SFGK 200	0157501	20	10	22		32	80	40	M8x1	1.1
	SFGL 200	0157121	20	10	22		32	110	40	M8x1	1.5
	STB 200	0156099	17		22	45	61	80		M12	3.4


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 200	0155101	10	20	22	42	38	71.7	10	40	M8	Stahl	2.4


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	STF 200	0161101	22	60	35	94	10	Stahl	1.9


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	34 - 99	267	I	SZKA 212	0139153	10	20	26	45	25	M6	40	M8	Stahl	1.4
	109 - 175	267	I	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Stahl	1.3
	144 - 210	272	I	SZKA 216	0139159	10	20	30	45	25	M6	40	M8	Stahl	1.2
	64 - 127	267	II	SZKA 213	0139154	10	20	30	45	25	M6	40	M8	Stahl	1.3

Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	54 - 113	266	I	SZKI 209	0166154	10	20	30	45	20	M6	40	M8	Stahl	1.7
	117 - 183	266	I	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Stahl	1.4
	82 - 136	266	II	SZKI 211	0166156	10	20	30	45	20	M6	40	M8	Stahl	1.4



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	14 - 78	267	II	SZKA-ST 201	0182152	10	20	22	45	37	40	M8	Stahl	0.9

Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 200	0173101	10	20	140	64	200	60	56	50	70	27	40	M8	Stahl	9
	SFA-SM 201	0173105	10	20	140	64	200	80	76	70	70	27	40	M8	Stahl	12.5
	SFA-SA 200	0174101	10	20	140	50	200	58	54	48	72.5	32	40	M8	Aluminium	3.5
	SFA-SA 201	0174105	10	20	140	50	200	80	76	70	72.5	32	40	M8	Aluminium	4.7

