






Grundbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Schrauben	m/Satz [kg]
	SFG 250	0157102	20	12	26		37	110		40	M12x1.5	2
	SFGL 250	0157112	20	12	26		37	122		40	M12x1.5	2.3
	STB 250-1	0156100	17		26	45	65	110			M12	4.9
	STB 250-2	0156101	21		26	54	70	110			M16	5.2
	STN 250-4	0160501	21		26	45	50	110	13	28	M16	4.2


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Stahl	1.9


Harte Stufenblockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Werkstoff	m/Satz [kg]
	STF 250	0161102	26	70	40	114	14	Stahl	3.3


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	153 - 234	328	I	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Stahl	1.9
	186 - 267	342	I	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Stahl	2.2
	31 - 101	325	II	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Stahl	1.4
	78 - 158	325	II	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Stahl	1.9


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	73 - 152	324	I	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Stahl	2.8
	190 - 271	325	I	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2
	115 - 196	324	II	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Stahl	2.2



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Grundbacken- stellung	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	13 - 84	325	II	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Stahl	1.2



Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	67 - 110	298	PNK-G 315-2	0190611	93	40	2.6
	97 - 153	332	PNK-G 315-4	0190613	93	40	2.8
	149 - 207	332	PNK-G 315-6	0190615	93	40	3.1
	163 - 217	332	PNK-G 315-8	0190617	93	40	4
	57 - 91	274	PNK-S 250-2	0190551	86	40	2.4
	85 - 108	288	PNK-S 250-6	0190555	86	40	2.7
	119 - 180	305	PNK-S 250-8	0190557	86	40	2.6
	128 - 194	310	PNK-S 250-10	0190559	86	40	2.7


QUENTES Kunststoffbacken

	Spannbereich ØD	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Schrauben	m/Satz [kg]
	55 - 124	TRQK 250-2	0150012	12	20	40	57	72	40	M12	0.7
	20 - 98	TRQK 250-1	0150011	12	20	38	53	98	40	M12	0.8



Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Stahl	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Stahl	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Stahl	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Stahl	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Stahl	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Stahl	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Stahl	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Stahl	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Stahl	20.9
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminium	2.1

Weiche Blockbacken

	Bezeichnung	Ident.-Nr.	B [mm]	H [mm]	H1 [mm]	L [mm]	Werkstoff	m/Satz [kg]
	SMB 250	0163102	26	70	40	115	Stahl	4.4
	SMB-H 250	0163202	26	100	70	115	Stahl	6.5

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Stahl	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Stahl	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminium	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminium	6.4

