




Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a [mm]	Min. Abstand b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	SBM 41	0112112	21	50	60	90	15	28	M16	Stahl	2.1
	SBM 42	0112113	21	50	60	105	15	28	M16	Stahl	2.4
	SBM 4210	0112115	21	50	100	120	15	28	M16	Stahl	5
	SBM 4212	0112116	21	50	120	120	15	28	M16	Stahl	5.6
	SBM 4215	0112117	21	50	150	120	15	28	M16	Stahl	7
	SBM 428	0112114	21	50	80	120	15	28	M16	Stahl	3.7
	SBM 4281	0112137	21	50	80	150	15	28	M16	Stahl	4.6
	SBM 43	0112118	21	60	60	90	15	28	M16	Stahl	2.4
	SBM 44	0112119	21	60	60	105	15	28	M16	Stahl	2.9
	SBM 45	0112120	21	60	80	90	15	28	M16	Stahl	3.2
	SBM 46	0112121	21	60	80	105	15	28	M16	Stahl	3.8
	SBM 47	0112122	21	60	80	120	15	28	M16	Stahl	4.4
	SBM 48	0112123	21	80	60	90	15	28	M16	Stahl	3.2
	SBM 498	0112125	21	80	80	120	15	28	M16	Stahl	5.8


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 250	0121105	21	50	58	103.5	14	34	25	25	M16	Stahl	3.5
	SHB 315	0121111	21	50	58	128	14	46	30	30	M16	Stahl	4.6


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	82 – 159	332	SZA 25-37	0138180	21	50	58	25	M8	28	M16	Stahl	3.3
	122 – 199	332	SZA 25-38	0138181	21	50	58	25	M8	28	M16	Stahl	2.9
	172 – 249	336	SZA 25-39	0138182	21	50	58	25	M8	28	M16	Stahl	2.7
	219 – 296	371	SZA 25-40	0138183	21	50	58	25	M8	28	M16	Stahl	3.2
	59 – 136	341	SZA 31-10	0138184	21	50	58	25	M8	28	M16	Stahl	3.4
	117 – 194	343	SZA 31-11	0138185	21	50	58	25	M8	28	M16	Stahl	3.4
	183 – 260	341	SZA 31-12	0138186	21	50	58	25	M8	28	M16	Stahl	3.2
	246 – 324	401	SZA 31-13	0138187	21	50	58	25	M8	28	M16	Stahl	4.5


Krallenbacken für Innenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	111 – 187	339	SZI 25-34	0123183	21	50	58	25	M8	28	M16	Stahl	3.5
	152 – 229	342	SZI 25-35	0123184	21	50	58	25	M8	28	M16	Stahl	3.2
	198 – 275	341	SZI 25-36	0123185	21	50	58	25	M8	28	M16	Stahl	3
	82 – 157	348	SZI 31-11	0123186	21	50	58	25	M8	28	M16	Stahl	4.1
	134 – 211	341	SZI 31-12	0123187	21	50	58	25	M8	28	M16	Stahl	4.2
	208 – 286	340	SZI 31-13	0123188	21	50	58	25	M8	28	M16	Stahl	3.9



Krallenbacken für Stangenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	52 - 129	334	SZA-ST 25-2	0175103	21	45	50	40	28	M16	Stahl	2.7
	22 - 97	341	SZA-ST 31-1	0175104	21	45	50	40	28	M16	Stahl	3.3




Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	108 - 137	297	PNS-Z 250-21-3	0190107	64	35	2.1
	160 - 182	307	PNS-Z 250-21-4	0190108	64	35	2.3
	169 - 201	318	PNS-Z 250-21-5	0190109	64	35	2.3
	88 - 111	291	PNS-Z 315-1	0190110	64	35	2
	102 - 160	331	PNS-Z 315-2	0190111	64	35	2.3
	165 - 211	334	PNS-Z 315-3	0190112	64	35	2.5
	175 - 233	350	PNS-Z 315-4	0190113	64	35	2.7
	201 - 233	352	PNS-Z 315-5	0190114	64	35	3.2



Verzahnte Stangen

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 210	0112180	21	50	60	420	Stahl	9.4
	SBM-ST 211	0112181	21	50	80	420	Stahl	12.7
	SBM-ST 212	0112182	21	50	120	420	Stahl	19.3
	SBM-ST 213	0112183	21	80	80	420	Stahl	20.4
	SBM-STA 210	0112184	21	50	80	420	Aluminium	4.6


Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWBL 250-21	0120155	21	50	50	120	4	20	28	M16	Stahl	5.6
	SWBL 315	0120156	21	50	50	140	4	30	28	M16	Stahl	6.5
	2 SWK 200	0126102	21	80	80	95		22	28	M16	Stahl	8.2
	CWB 251	0100012	21	50	60	95		15	28	M16	Stahl	5.2
	SWB 250	0120105	21	50	80	120		30	28	M16	Stahl	9.4
	SWB-FR 315	0120406	21	50	60	105		15	25	M16	Stahl	6
	SWB-AL 250	0168102	21	50	80	120		30	28	M16	Aluminium	3

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-SM 251	0169107	21	180	104	250	100	85	80	30	28	M16	Stahl	21.7
	SWB-SM 315	0169104	21	240	120	320	70	55	110	60	28	M16	Stahl	26.6
	SWB-SA 250-21	0170103	21	180	70	250	78	63	87.5	40	28	M16	Aluminium	7.3
	SWB-SA 251	0170107	21	180	70	250	100	85	87.5	40	28	M16	Aluminium	8.3
	SWB-SA 315	0170104	21	240	80	320	78	63	117	70	28	M16	Aluminium	12

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NKS 3	0143107	21	26.5	10		M16	M16 x 35	150
	NKA 3	0145105	21	26.5	10	28	M16	M16 x 35	150

