




Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SHB 130	0121100	12	30	38	57	10	16	15	15	M8	Stahl	0.7


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	39 - 68	178	SZA 16-10	0122250	12	32	40	20	M5	15	M8	Stahl	1
	67 - 96	176	SZA 16-11	0122251	12	32	40	20	M5	15	M8	Stahl	1
	87 - 117	176	SZA 16-12	0122252	12	32	40	20	M5	15	M8	Stahl	0.9



Krallenbacken für Innenspannung

	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	178	SZI 16-15	0123157	12	30	40	15	M5	15	M8	Stahl	1
	178	SZI 16-16	0123158	12	30	40	15	M5	15	M8	Stahl	1
	184	SZI 16-17	0123159	12	30	40	15	M5	15	M8	Stahl	0.7

Krallenbacken für Stangenspannung




	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	14 - 38	181	SZA-ST 16-4	0175112	12	32	40	30	15	M8	Stahl	1.1

Verzahnte Stangen



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	SBM-ST 120	0112160	12	35	60	420	Stahl	6.7
	SBM-ST 121	0112163	12	40	80	420	Stahl	10.2
	SBM-STA 120	0112161	12	35	60	420	Aluminium	2.4




Weiche Aufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SWB-FR 162	0120409	12	35	40	72	3	12	15	M8	Stahl	1.6
	SWB 130	0120100	12	30	38	55.5		10	16	M8	Stahl	1.2
	SWB-FF 130	0120300	12	32	32	60		12	19	M10	Stahl	1.1
	SWB-FB 235	0120204	12	30	55.5	84		18	21	M12	Stahl	2.6
	SWB-FB 237	0120201	12	35	60	90		14	21	M12	Stahl	3.7
	SWB-FR 160	0120402	12	30	38	55.5		9	15	M8	Stahl	1.2
	SWB-FR 161	0120403	12	30	55.5	55		9	15	M8	Stahl	1.8
	FR-AL 160	0120601	12	30	55	70		9	15	M8	Aluminium	0.9
	SWB-AL 130	0168104	12	30	40	55		10	16	M8	Aluminium	0.45

Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	FR-SM 160	0120701	12	120	40	160	60	50	60	20	15	15	M8	Stahl	6
	FR-SA 160	0120651	12	120	40	165	58	48	59.5	18	15	15	M8	Aluminium	2.1

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NS 80	0140100	12	17.2	7		M8	M8 x 22	30
	NK 81	0147106	12	17.2	7	15	M8	M8 x 22	30