




# SCHUNK Spannbacken für SPK 180

Spannklauenkästen

## Harte Stufenaufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | T<br>[mm] | a<br>[mm] | b<br>[mm] | c<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | SHB 400     | 0121107    | 25.5      | 60        | 75        | 140       | 18        | 53        | 31        | 31        | M20       | Stahl     | 8              |

## Weiche Aufsatzbacken

|                                                                                   | Bezeichnung | Ident.-Nr. | N<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | a<br>[mm] | b<br>[mm] | Schrauben | Werkstoff | m/Satz<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|------------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|----------------|
|  | CWB 400     | 0100008    | 25.5      | 60        | 80        | 140       | 30        | 35        | M20       | Stahl     | 12.6           |
|                                                                                   | SWB 400     | 0120107    | 25.5      | 60        | 90        | 155       | 30        | 35        | M20       | Stahl     | 16             |
|  | SWB-AL 400  | 0168103    | 25.5      | 60        | 100       | 155       | 30        | 35        | M20       | Aluminium | 6.4            |

## Nutenstein

|                                                                                     | Bezeichnung | Ident.-Nr. | S<br>[mm] | H<br>[mm] | H1<br>[mm] | G   | Zyl.-Schraube | Max. zul.<br>Anziehdrehmoment<br>[Nm] |
|-------------------------------------------------------------------------------------|-------------|------------|-----------|-----------|------------|-----|---------------|---------------------------------------|
|  | NS 200      | 0140103    | 25.5      | 29        | 11         | M20 | M20 x 40      | 220                                   |



Technische Beratung und Verkauf: Tel. +49-7133-103-2750