




### Base Jaws

|                                                                                   | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | L<br>[mm] | b<br>[mm] | Screws | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|---------------|
|  | SFG 160     | 0157100 | 18        | 8         | 20        | 27        | 74        | 32        | M8x1   | 0.8           |
|                                                                                   | SFGK 160    | 0157500 | 18        | 8         | 20        | 27        | 64        | 32        | M8x1   | 0.7           |


### Claw jaws For bar clamping

|                                                                                   | Clamping range ØD | Swing diameter SDmax | Position of base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-----------------------------------------------------------------------------------|-------------------|----------------------|-----------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | 10 - 42           | 208                  | II                    | SZKA-ST 161 | 0182150 | 8         | 18        | 22        | 40        | 30        | 32        | M8     | Steel    | 0.8           |


### Claw jaws for I.D. clamping

|                                                                                    | Clamping range ØD | Swing diameter SDmax | Position of base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|------------------------------------------------------------------------------------|-------------------|----------------------|-----------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | 55 - 90           | 206                  | I                     | SZKI 168    | 0166151 | 8         | 18        | 35        | 40        | 20        | M6        | 32        | M8     | Steel    | 1.4           |
|                                                                                    | 110 - 145         | 206                  | I                     | SZKI 169    | 0166152 | 8         | 18        | 30        | 40        | 20        | M6        | 32        | M8     | Steel    | 1.3           |


### Claw jaws for O.D. clamping

|                                                                                     | Clamping range ØD | Swing diameter SDmax | Position of base jaws | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | T<br>[mm] | G<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------------|----------------------|-----------------------|-------------|---------|-----------|-----------|-----------|-----------|-----------|-----------|-----------|--------|----------|---------------|
|  | 98 - 134          | 214                  | I                     | SZKA 163    | 0165146 | 8         | 18        | 40        | 40        | 20        | M6        | 32        | M8     | Steel    | 1             |
|                                                                                     | 51 - 86           | 207                  | I                     | SZKA 169    | 0165174 | 8         | 18        | 26        | 40        | 20        | M6        | 32        | M8     | Steel    | 1             |
|                                                                                     | 63 - 99           | 208                  | II                    | SZKA 163    | 0165146 | 8         | 18        | 40        | 40        | 20        | M6        | 32        | M8     | Steel    | 1             |
|                                                                                     | 114 - 150         | 211                  | II                    | SZKA 167    | 0165150 | 8         | 18        | 30        | 40        | 20        | M6        | 32        | M8     | Steel    | 1.3           |

### Hard Stepped Block Jaws


|                                                                                     | Description | ID      | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|------------|-----------|-----------|----------|---------------|
|  | STF 160     | 0161100 | 20        | 45        | 24         | 79        | 7.5       | Steel    | 1.1           |

### Hard Stepped Top Jaws



|                                                                                     | Description | ID      | N<br>[mm] | S<br>[mm] | B<br>[mm] | H<br>[mm] | H1<br>[mm] | L<br>[mm] | T<br>[mm] | b<br>[mm] | Screws | Material | m/set<br>[kg] |
|-------------------------------------------------------------------------------------|-------------|---------|-----------|-----------|-----------|-----------|------------|-----------|-----------|-----------|--------|----------|---------------|
|  | SHF 160     | 0155100 | 8         | 18        | 20        | 36.5      | 32.5       | 63        | 7.5       | 32        | M8     | Steel    | 0.6           |




### QUENTES fiberglass jaws

|                                                                                   | Clamping range ØD | Description | ID      | N [mm] | S [mm] | B [mm] | H [mm] | L [mm] | b [mm] | Screws | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------------|-------------|---------|--------|--------|--------|--------|--------|--------|--------|------------|
|  | 20 - 71           | TRQK 160    | 0150024 | 8      | 18     | 38     | 54     | 56     | 32     | M8     | 0.5        |



### Soft Full Grip Jaws

|                                                                                   | Description | ID      | N [mm] | S [mm] | B [mm] | B1 [mm] | Ø D [mm] | H [mm] | H1 [mm] | H2 [mm] | L [mm] | L1 [mm] | b [mm] | Screws | Material | m/set [kg] |
|-----------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|---------|----------|--------|---------|---------|--------|---------|--------|--------|----------|------------|
|  | SFA-SM 160  | 0173100 | 8      | 18     | 120    | 40      | 160      | 50     | 46      | 40      | 60     | 23      | 32     | M8     | Steel    | 4.8        |
|  | SFA-SA 160  | 0174100 | 8      | 18     | 120    | 40      | 165      | 50     | 46      | 40      | 59.5   | 23      | 32     | M8     | Aluminum | 1.8        |

### Soft Monoblock Jaws

|                                                                                     | Description | ID      | B [mm] | H [mm] | H1 [mm] | L [mm] | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|---------|--------|----------|------------|
|  | SMB 160     | 0163100 | 20     | 45     | 24      | 79     | Steel    | 1.5        |
|                                                                                     | SMB-H 160   | 0163200 | 20     | 60     | 39      | 79     | Steel    | 2          |

### Soft Top Jaws

|                                                                                     | Description | ID      | N [mm] | S [mm] | B [mm] | H [mm] | H1 [mm] | H2 [mm] | L [mm] | L1 [mm] | b [mm] | Screws | Material | m/set [kg] |
|-------------------------------------------------------------------------------------|-------------|---------|--------|--------|--------|--------|---------|---------|--------|---------|--------|--------|----------|------------|
|  | SFA 160     | 0153100 | 8      | 18     | 20     | 40     | 36      |         | 85     | 25      | 32     | M8     | Steel    | 1.2        |
|                                                                                     | SFA 160-C1  | 0154121 | 8      | 18     | 30     |        | 55.5    | 51.5    | 85     | 19      | 32     | M8     | Steel    | 2.7        |
|                                                                                     | SFA 160-C2  | 0154127 | 8      | 18     | 35     |        | 40      | 36      | 63     | 19      | 32     | M8     | Steel    | 1.6        |
|                                                                                     | SFA 160-C3  | 0154131 | 8      | 18     | 40     |        | 60      | 56      | 70     | 19      | 32     | M8     | Steel    | 3.3        |
|                                                                                     | SFA 160-C4  | 0154133 | 8      | 18     | 40     |        | 80      | 76      | 85     | 19      | 32     | M8     | Steel    | 5.6        |
|  | SFA-AL 160  | 0172100 | 8      | 18     | 25     | 50     | 46      |         | 85     | 25      | 32     | M8     | Aluminum | 0.7        |

