





Backenrohlinge

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Min. Abstand a [mm]	Min. Abstand b [mm]	Schrauben	Werkstoff	m/Stück [kg]
	JBW 80	0114404	14	40	80	95	13	25	M12	Stahl	2.4
	JBW 81	0114400	14	40	40	70	13	25	M12	Stahl	0.9
	JBW 82	0114401	14	40	40	95	13	25	M12	Stahl	1.2
	JBW 83	0114402	14	40	60	70	13	25	M12	Stahl	1.3
	JBW 84	0114403	14	40	60	95	13	25	M12	Stahl	1.7
	JBW 85	0114405	14	40	100	95	13	25	M12	Stahl	2.9
	JBW 86	0114406	14	60	60	70	13	25	M12	Stahl	2
	JBW 87	0114407	14	80	60	70	13	25	M12	Stahl	2.6


Harte Stufenaufsatzbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	HSKN 215	0129101	14	36	52.5	81	12	25	21	21	M10	Stahl	1.85
	SHB-J 80	0133109	14	35	51	87	12	15.5	25	25	M12	Stahl	1.85
	SHB-J 82	0133110	14	32	38	79	12	16	25	25	M12	Stahl	1.2


Krallenbacken für Außenspannung

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	44 – 71	221	SZAJ 20-1	0138110	14	35	53	25	M6	25	M12	Stahl	1.9
	71 – 99	222	SZAJ 20-2	0138112	14	35	53	25	M6	25	M12	Stahl	1.6
	102 – 129	221	SZAJ 20-3	0138114	14	40	53	25	M6	25	M12	Stahl	1.7
	132 – 160	223	SZAJ 20-4	0138116	14	40	53	25	M6	25	M12	Stahl	1.6
	153 – 182	240	SZAJ 20-16	0138143	14	40	53	25	M6	25	M12	Stahl	1.7

Krallenbacken für Innenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	60 – 87	225	SZIJ 20-1	0179110	14	35	53	20	M6	25	M12	Stahl	2
	89 – 117	226	SZIJ 20-2	0179111	14	40	53	20	M6	25	M12	Stahl	2.1
	120 – 147	222	SZIJ 20-3	0179113	14	40	53	20	M6	25	M12	Stahl	2.1
	149 – 177	232	SZIJ 20-4	0179114	14	40	53	20	M6	25	M12	Stahl	2

Krallenbacken für Stangenspannung


	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	28 – 49	219	SZAJ-ST 20-2	0175503	14	35	45	38	25	M12	Stahl	1.8







Pendelbacken

	Spannbereich ØD	Schwingkreis SDmax	Bezeichnung	Ident.-Nr.	H [mm]	T [mm]	m/Stück [kg]
	68 – 87	219	PNS-M 200-14-1	0160232	55	30	1.3
	99 – 118	241	PNS-M 200-14-2	0160233	55	30	1.5
	129 – 148	239	PNS-M 200-14-3	0160234	55	30	1.6

Verzahnte Stangen



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	Werkstoff	m/Stück [kg]
	JBM-ST 140	0114520	14	40	80	420	Stahl	10.2
	JBM-ST 141	0114521	14	60	60	420	Stahl	11.2
	JBM-STA 140	0114522	14	40	80	420	Aluminium	3.7

Weiche Aufsatzbacken



	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	H [mm]	L [mm]	M [mm]	a1 [mm]	a [mm]	b [mm]	c [mm]	Schrauben	Werkstoff	m/Satz [kg]
	SKN 215	0127103	14	35	60	89	34		18	26		M10	Stahl	3.6
	KM-WBL 80	0132601	14	35	40	102		4	20	25		M12	Stahl	2.7
	KM-WBL 81	0132607	14	40	80	102		4	20	25		M12	Stahl	6
	KM-WBL 82	0132615	14	40	100	102		4	20	25		M12	Stahl	7.6
	SKNL 215	0128101	14	40	42	102	34	3	16	22	22	M10	Stahl	2.9
	KM-WB 84	0132126	14	35	60	95			24	25		M12	Stahl	3.9
	KM-WB 85	0132127	14	40	80	95			24	25		M12	Stahl	6.1
	KM-WB 88	0132139	14	35	40	95			24	25		M12	Stahl	2.7
	KM-WBAL 80	0132522	14	40	60	90			20	25		M12	Aluminium	1.5



Weiche Segmentbacken

	Bezeichnung	Ident.-Nr.	N [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	L [mm]	a [mm]	b [mm]	Schrauben	Werkstoff	m/Satz [kg]
	KMWB-SM 210	0132701	14	140	70	200	60	50	70	30	25	M12	Stahl	8.8
	KMWB-SM 211	0132705	14	140	70	200	80	70	70	30	25	M12	Stahl	11.7
	KMWB-SA 210	0132801	14	140	50	200	58	48	72.5	35	25	M12	Aluminium	3.3
	KMWB-SA 211	0132805	14	140	50	200	80	70	72.5	35	25	M12	Aluminium	4.5

Nutenstein

	Bezeichnung	Ident.-Nr.	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Zyl.-Schraube	Max. zul. Anziehdrehmo- ment [Nm]
	NJ 82	0146131	14	20.5	8.5	25	M12	M12 x 30	70
	NJ 82 gesägt/ sawn	0146005	14	20.5	8.5		M12	M12 x 30	70

