





Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	L1 [mm]	b [mm]	Screws	m/set [kg]
	SFGF-K 1400	8705289	40	24	65	58	280	136	82	M20	16.2
	SFGF-L 1400	8705286	40	24	65	58	570	118	82	M20	36.9



Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	288 - 1101	1408	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	445 - 1262	1408	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 630	0155106	24	40	65	105	97	185	30	82	M20	Steel	18

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 630	0153106	24	40	65	118	110	260	70	82	M20	Steel	39.6
	SFA-AL 630	0172106	24	40	65	118	110	260	70	82	M20	Aluminum	14.8

