






Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	GBK 250	0159101	20	12	26		37	104		40	M12	1.8
	GBKL 250	0159121	20	12	26		37	125		40	M12	2.4
	GBK-V 250	0159151	20	12	26		37	104		40	M12	1.8
	STB-G 250-2	0160657	21		26	50	71	104			M16	5.2
	STNJ 250-5	0160651	16		26	40	49	110	10	30	M12	2.9
	STN 250-5	0160600	17		26	40	48	86	10	22	M12	2.6
	STN 250-6	0160601	21		26	45	52	110	13	28	M16	4


Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	13 - 90	319	II	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Steel	1.2


Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	69 - 146	318	I	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Steel	2.8
	181 - 265	319	I	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2
	117 - 202	319	II	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2

Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	86 - 170	322	I	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	143 - 228	322	I	SZKA 266	0139163	12	20	40	50	25	M6	40	M12	Steel	1.9
	177 - 262	336	I	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2
	31 - 107	319	II	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4


Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 251	0162105	26	65	36	107.4	10	Steel	2.8




Technical advice and sales: Tel. +49-7133-103-2750



Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Steel	1.9



Pendulum jaws

	Clamping range ØD	Swing diameter SDmax	Description	ID	H [mm]	T [mm]	m/piece [kg]
	56 - 92	275	PNK-G 250-2	0190601	86	40	1.8
	85 - 123	306	PNK-G 250-6	0190605	86	40	2.2
	118 - 181	305	PNK-G 250-8	0190607	86	40	2.4
	127 - 198	315	PNK-G 250-10	0190609	86	40	2.5

QUENTES fiberglass jaws




	Clamping range ØD	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	55 - 124	TRQK 250-2	0150012	12	20	40	57	72	40	M12	0.7
	20 - 98	TRQK 250-1	0150011	12	20	38	53	98	40	M12	0.8

Soft Full Grip Jaws



	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	Ø D [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA-SM 250	0173102	12	20	180	70	250	60	55	45	90	44	40	M12	Steel	12.8
	SFA-SM 251	0173106	12	20	180	70	250	80	75	65	90	44	40	M12	Steel	16.8
	SFA-SA 250	0174102	12	20	180	70	250	58	53	43	87.5	44	40	M12	Aluminum	4.8
	SFA-SA 251	0174106	12	20	180	70	250	80	75	65	87.5	44	40	M12	Aluminum	6.4



Soft Monoblock Jaws

	Description	ID	B [mm]	B1 [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	Material	m/set [kg]
	UVB 250	0164101	26		84	55		99	Steel	4.8
	UVB-H 250	0164117	26		115	86		99	Steel	6.6
	UVB-B 250	0164114	26	46	84	52		99	Steel	7.2
	UVB-HS 250	0164120	26		115	86	48	99	Steel	5.25

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	H2 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 250	0153102	12	20	30	55.5	50.5		125	35	40	M12	Steel	3.7
	SFA 250-C1	0154101	12	20	40		60	55	90	26	40	M12	Steel	3.9
	SFA 250-C2	0154102	12	20	40		60	55	125	26	40	M12	Steel	5.6
	SFA 250-C3	0154103	12	20	40		80	75	125	26	40	M12	Steel	7.7
	SFA 250-C4	0154104	12	20	40		100	95	125	26	40	M12	Steel	9.8
	SFA 250-C5	0154105	12	20	40		120	115	125	26	40	M12	Steel	11.8
	SFA 250-C6	0154106	12	20	60		60	55	90	26	40	M12	Steel	6
	SFA 250-C7	0154107	12	20	80		60	55	90	26	40	M12	Steel	8.5
	SFA 250-C8	0154134	12	20	80		100	95	125	26	40	M12	Steel	20.9
	SFA-AL 250	0172103	12	20	40	60	55		125	35	40	M12	Aluminum	2.1

