




Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	L [mm]	b [mm]	Screws	m/set [kg]
	SFG 1000	0157108	40	24	65	68	314	82	M20	24.4


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Position of base jaws	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	544 - 891	1194	I	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	705 - 1052	1194	I	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8
	206 - 551	1026	II	SZKA 631	0139200	24	40	65	97	42	M8	82	M20	Steel	13
	366 - 712	1026	II	SZKA 632	0139201	24	40	65	97	42	M8	82	M20	Steel	11.8



Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 630	0155106	24	40	65	105	97	185	30	82	M20	Steel	18

Soft Monoblock Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	Material	m/set [kg]
	SMB 630-800	0163106	65	130	88	230	Steel	40

Soft Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	L1 [mm]	b [mm]	Screws	Material	m/set [kg]
	SFA 630	0153106	24	40	65	118	110	260	70	82	M20	Steel	39.6
	SFA 1000	0153108	24	40	76	150	142	350	70	82	M20	Steel	87
	SFA-AL 1000	0172108	24	40	80	155	147	350	70	82	M20	Aluminum	32

