



Claw jaws For bar clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	31 - 73	270	SZAJ-ST 25-3	0175508	16	40	50	44	30	M12	Steel	2.5



Claw jaws for I.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	62 - 112	277	SZIJ 25-1	0179116	16	40	58	25	M6	30	M12	Steel	2.7
	94 - 152	277	SZIJ 25-2	0179118	16	40	58	25	M6	30	M12	Steel	2.8
	125 - 190	272	SZIJ 25-3	0179120	16	40	58	25	M6	30	M12	Steel	2.4
	158 - 224	282	SZIJ 25-4	0179121	16	40	58	25	M6	30	M12	Steel	2.2


Claw jaws for O.D. clamping

	Clamping range ØD	Swing diameter SDmax	Description	ID	N [mm]	B [mm]	H [mm]	T [mm]	G [mm]	b [mm]	Screws	Material	m/set [kg]
	44 - 118	268	SZAJ 20-5	0138120	16	35	53	25	M6	25	M12	Steel	1.8
	71 - 146	269	SZAJ 20-6	0138125	16	35	53	25	M6	25	M12	Steel	1.6
	101 - 176	268	SZAJ 20-7	0138122	16	40	53	25	M6	25	M12	Steel	1.7
	131 - 207	269	SZAJ 20-8	0138127	16	40	53	25	M6	25	M12	Steel	1.6
	39 - 94	273	SZAJ 25-1	0138117	16	40	58	25	M6	30	M12	Steel	2.9
	72 - 136	275	SZAJ 25-2	0138119	16	40	58	25	M6	30	M12	Steel	2.3
	115 - 181	279	SZAJ 25-3	0138121	16	40	58	25	M6	30	M12	Steel	2.1
	160 - 226	293	SZAJ 25-4	0138123	16	40	58	25	M6	30	M12	Steel	2.3
	195 - 261	325	SZAJ 25-15	0138118	16	40	58	25	M6	30	M12	Steel	2.8




Hard Stepped Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	T [mm]	a [mm]	b [mm]	c [mm]	Screws	Material	m/set [kg]
	SHB-J 100	0133111	16	40	54	101.5	13	25.5	30	30	M12	Steel	2.8
	SHB-J 102	0131109	16	35	42	83	15	19	25	25	M12	Steel	1.5




[illegible]

Soft Top Jaws

	Description	ID	N [mm]	B [mm]	H [mm]	L [mm]	a1 [mm]	a [mm]	b [mm]	Screws	Material	m/set [kg]
	H-WBL 82	0130602	16	40	40	102	4	20	25	M12	Steel	3
	KM-WBL 100	0132602	16	40	42	125	4	30	30	M12	Steel	4.1
	KM-WBL 101	0132608	16	40	100	125	4	30	30	M12	Steel	9.8
	KM-WBL 103	0132609	16	40	60	125	4	30	30	M12	Steel	5.7
	H-WB 82	0130120	16	40	60	86		20	25	M12	Steel	4.1
	H-WB 84	0132146	16	40	40	85		20	25	M12	Steel	2.6
	KM-WB 102	0132104	16	40	60	90		15	30	M12	Steel	4.3
	KM-WB 103	0132105	16	40	60	110		30	30	M12	Steel	5.2
	KM-WB 104	0132106	16	50	80	90		15	30	M12	Steel	7.3
	KM-WB 105	0132129	16	40	80	110		30	30	M12	Steel	7.2
	KM-WB 106	0132152	16	40	100	120		30	30	M12	Steel	9.9
	KM-WB 110	0132140	16	40	42	110		30	30	M12	Steel	3.8
	KM-WB 111	0132147	16	50	50	120		30	30	M12	Steel	6.2
	H-WBAL 81	0130503	16	40	60	90		20	25	M12	Aluminum	1.5
	KM-WBAL 100	0132523	16	40	60	110		25	30	M12	Aluminum	1.9

T-nut

	Description	ID	S [mm]	H [mm]	H1 [mm]	b [mm]	G	Cyl.-screw	Max. adm. tightening torque [Nm]
	NJ 103	0146132	16	21.5	8.5	30	M12	M12 x 30	70
	NJ 103 gesägt/sawn	0146002	16	21.5	8.5		M12	M12 x 30	70

