




SCHUNK chuck jaws for ROTA THW3 315-104


Base Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	B1 [mm]	H [mm]	L [mm]	a [mm]	b [mm]	Screws	m/set [kg]
	GBK 315	0159102	20	12	32		43	115		40	M12	3
	GBKL 315	0159122	20	12	32		43	137		40	M12	3.5
	GBK-V 315	0159152	20	12	32		43	115		40	M12	3
	STNJ 315-5	0160652	18		32	50	54	120	15	30	M14	4.9
	STNJ 315-6	0160665	21		32	50	58	125	17.5	30	M16	5.5
	STN 315-6	0160603	21		32	45	56	110	13	28	M16	4.5


Claw jaws For bar clamping

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SZKA-ST 251	0182154	12	20	26	45	35	40	M12	Steel	1.2


Claw jaws for I.D. clamping

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	SZKI 261	0166158	12	20	40	50	25	M6	40	M12	Steel	2.8
	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2
	SZKI 264	0166161	12	20	40	50	25	M6	40	M12	Steel	2.2


Claw jaws for O.D. clamping

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	Material	m/set [kg]
	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2
	SZKA 263	0139160	12	20	30	50	25	M6	40	M12	Steel	1.4
	SZKA 268	0139165	12	20	40	50	25	M6	40	M12	Steel	2.2

Hard Stepped Block Jaws

	Description	ID	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	Material	m/set [kg]
	GST 315	0162102	32	66	32	116.3	10	Steel	3.5

Hard Stepped Top Jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	H1 [mm]	L [mm]	T [mm]	b [mm]	Screws	Material	m/set [kg]
	SHF 250	0155102	12	20	30	55	50	90	14	40	M12	Steel	1.9



Technical advice and sales: Tel. +49-7133-103-2750

SCHUNK chuck jaws for ROTA THW3 315-104

Pendulum jaws

Technical drawing of a mechanical part, likely a bracket or support, showing dimensions: D , d , L , B_1 , B_2 , H , and a curved surface with radius R .

QUENTES fiberglass jaws

Soft Monoblock Jaws

A 3D perspective diagram of a rectangular block. The top horizontal edge is labeled L . The front bottom edge is labeled B . The total height is labeled H . A dashed line indicates a horizontal cut at a height of H_1 from the bottom. The block is dark gray with a lighter gray base.


A 3D perspective view of a rectangular block. The top surface is labeled with length L and width B_1 . The front face is labeled with height H_1 . The total height of the block is labeled H . The base of the block is labeled b . A dashed line indicates a horizontal cut or internal feature at height H_1 .

Soft Top Jaws



SCHUNK chuck jaws for ROTA THW3 315-104

Universal top jaws

	Description	ID	N [mm]	S [mm]	B [mm]	H [mm]	T [mm]	G	b [mm]	Screws	m/set [kg]
	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6
	SZKU 250	0139302	12	20	30	55	25	M6	40	M12	1.6



Technical advice and sales: Tel. +49-7133-103-2750